

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -




ALL RIGHTS RESERVED.

CONNECTOR TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE B (WITH EXTERNAL SPRING)

SECTION A-A


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
P2		REVISED PER ECO-17-008827	29JUN2017	AP	MP



TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV FOR JPT CONT. P/N 929939-...
A/O 929937-... AND REL. SINGLE WIRE SEAL
P/N 828904-1, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)

DIAM (ISOLANTE) (INS. DIA. RANGE)	RANGE FILO (WIRE RANGE)
1.5-3.0 mm (RED. INS. CABLE)	0.5-2.5 mm ²



ASSE CAVITA'
(CAVITY CENTER
LINE)

ASSE CONNETTORE
(CONNECTOR CENTER
LINE)

NERO (BLACK)	2-282191-1 P1	1				
NERO (BLACK)	1-282191-1	SUPERSEDED BY 282191-1				
ROSSO (RED)	---	CUSTOMER DRAWING FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
GIALLO (YELLOW)	---	P1	3	\\\\\\\\\\\\\\	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
MARRONE (BROWN)	282191-6					
BLU (BLUE)	282191-5					
VERDE (GREEN)	282191-4					
NATURALE (NATUR)	282191-3					
GRIGIO (GREY)	282191-2					
NERO (BLACK)	282191-1					
COLORE (COLOR)	NUMERO PART NO.	ASSY REV	NO. (ITEM)	FINITURA/COLORE (FINISH/COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 9 NOV 90

CHK E. CINI

CHK C. TARTARI

APVD 13 OCT 92

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±0.3
1 PLC	±0.3
2 PLC	±0.3
3 PLC	±0.3
4 PLC	±0.3
ANGLES	±2°

FINISH



TE Connectivity

NAME
3 W. SPLASH PROOF CONN. ASS'Y
WITH SECONDARY LOCK

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - C-282191

SCALE 2:1 SHEET 1 OF 2 REV P2

1 DIFFERISCE DAL ...-1 ESCLUSIVAMENTE PER IL PACKAGING
(DIFFERS FROM ...-1 ONLY FOR PACKAGING DETAILS)

2) PER DIMENSIONI CONTROPARTE VEDERE FOGLIO 2
(FOR COUNTERPART DIMENSIONS SEE SHEET 2)

