


										1
LOC	DIST	P	F	REVISIONS						
CF	39			ZONE	LTR	DESCRIPTION			DATE	APPD
		✓	✓		B	REV PER 0420-0472-96			6-13-96	KJH
					C	REV PER 0B20-1221-97			9-29-97	DKE
					D	REV PER 0B20-0566-98			5-5-98	DHW
					E	REV PER 0B20-1134-98			9-1-98	JRH





- 1 DENOTES SIGNAL SIDE.
2. LOCKWASHER, JAM NUT, GASKET OF ITEM #9 AND ITEM #10 PACKAGED UNASSEMBLED
- 3 ITEM #7 WHITE INK STAMPED STARTING WITH 1 THRU 9 FOR EACH APPROPRIATE LINE WITH 3.05[.12] HIGH CHARACTERS
4. IF ASSEMBLY IS MANUFACTURED OUTSIDE USA WHITE INK STAMP COUNTRY OF ORIGIN ON CONNECTOR
- 5 LABEL PRINTED WITH 1.5-3.0[.06-.12] HIGH BLACK CHARACTERS AS SHOWN;
- AMP
AMP P/N
AMP REV
DATE CODE

(DATE CODE = YEAR AND WEEK)
- 6 WHITE INK STAMP A NUMBER "1" AND REFERENCE DESIGNATION PER CHART, AS INDICATED.

AMP PART NUMBER	LENGTH	REFERENCE DESIGNATOR
621148-1	29.00	P 17
621148-2	48.00	P 13

1	1	LABEL	11
18	18	PANEL, BUSHING	10
9	9	JACK ASSY, BHD, SERIES BNC	9
9	9	FERRULE	8
9	9	TUBING, HEAT SHRINK	7
AR	AR	TUBING, HEAT SHRINK	6
AR	AR	RIBBON CABLE, COAX	5
2	2	SCREW	4
AR	AR	ADHESIVE, HOT MELT	3
2	2	CLAMP HALF	2
1	1	HOUSING ASSY	1
-2	-1	DESCRIPTION	ITEM NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± ____ 3 PLC DEC ± ____ ANGLES ± ____		DR 9/21/94 CHK 9/22/94 C. ADAMS APPD 9/22/94 C. ADAMS APPD 9/23/94 K. HEILIG PRODUCT SPEC 108-12036	AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL		APPLICATION SPEC	SIZE C	FSCM NO 00779
FINISH		WEIGHT	SCALE NTS	DRAWING NO 621148
			SHEET 1 OF 2	



WIRING DIAGRAM

621148-2
621148-1
PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 3 PLC DEC ± ANGLES ±		DR 9/21/94 CHK 9/22/94 C. ADAMS APPD 9/22/94 C. ADAMS APPD 9/23/94 K. HEILIG PRODUCT SPEC 108-12036 FINISH APPLICATION SPEC WEIGHT	AMP INCORPORATED Harrisburg, Pa. 17105 NAME LEAD ASSY, RIBBON COAX, 50 OHM, 25 WIDE SIZE C FSCM NO 00779 DRAWING NO 621148 SCALE NTS SHEET 2 OF 2	
---	--	---	---	--