





P.C. MOUNTING





CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = .0.4
X.XX = .0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 50mA @12VDC
5. CONTACT MATERIAL: SILVER
6. TRAVEL: 0.3 ± 0.15mm
- ▲ 7. OPERATING FORCE: 160 ± 50gf
8. CONTACT RESISTANCE: 100 mΩ max.
9. ELECTRICAL LIFE: 100,000 CYCLES min.
10. DIELECTRIC STRENGTH: 250V RMS min.
11. INSULATION RESISTANCE: 100 mΩ min.
12. ▲ DENOTES CRITICAL DIMENSION
13. 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



B	17963	REDRAWN, CORRECTED DIMENSIONS	2/11/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL1100CF160Q (6J BLK)

SCALE 3:1

DATE 2/11/2008

DR BLR

DWG XP0100A

REV B