





FED MFG CODE 91929

CATALOG LISTING
604HE1-6




—(12) NO. 20 WIRE LEAD PER MIL-W-22759/7 MARKED WITH IDENTIFICATION AND WIRE GAGE (1-20, 2-20, ETC) PER MIL-W- 5088

[illegible]

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE - - - - - 5-12 LB		CONTACT ARRANGEMENT	
FULL OVERTRAVEL FORCE - - - - 30 LB MAX		S P D T (4)	
RELEASE FORCE - - - - - 3 LB MIN		LOAD	28 VDC
PRETRAVEL - - - - - .040 MAX			SEA LEVEL & 50,000 FT
DIFFERENTIAL TRAVEL - - - - -.020 MAX		RES	7
OVERTRAVEL - - - - - .125 MIN		IND	4
		MOTOR	4

SCALE	FULL	
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$
THIRD ANGLE PROJECTION		
		
WEIGHT		

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 5
- 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 INCH OF PLUNGER TRAVEL
- 4 - CIRCUIT DIAGRAM, CATALOG LISTING, ARE SHOWN ON NAMEPLATE
- ⑤ REPLACEMENT MOUNTING HARDWARE - PACKET 19PA9
- 6 - OPERATION IN TEMPERATURE RANGE OF -65°F TO PLUS 257°F
- ⑦ HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805