


HONEYWELL
PART NUMBER
1SM379-H2
PRODUCT CODE
TWD3790

REV	DOCUMENT	CHANGED BY	CHECK
9	0034444	JA 16OCT07	PSR



NOTE -
⚠ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
2 - PLATED TERMINALS WILL ACCEPT AIRCRAFT MARINE PRODUCTS CO NO. 42429 CONNECTOR
3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400° F

RELEASE NO.:
PR-20752
REPLACES
-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± 0.040 ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± 0.0005 ANGLES ± 2		DRAWN	JA	16OCT07	Honeywell				
OPERATING FORCE----- 5-9 OZ		CONTACT ARRANGEMENT SPDT					CHECK	PSR	16OCT07					
RELEASE FORCE----- 2 OZ MIN		30 VOLTS DC RATING			THIRD ANGLE PROJECTION 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH-BASIC				
DIFFERENTIAL TRAVEL----- .008 MAX		SEA LEVEL 50,000 FT												
OVERTRAVEL----- .005 MIN		INDUCTIVE 3 AMP 2.5 AMP												
		RESISTIVE 5 AMP 5 AMP												
		MAXIMUM INRUSH 24 AMP												
APPROVALS		KEMA, CE	5A, 250V ~ T85 1E4				INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		UL, CSA	5A, 250 VAC							BRAND L4	B	I	1SM379-H2	
							RASTER			SCALE -	WEIGHT .006 LB MAX		SHEET 1 OF 1	