

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION, 19

(C) COPYRIGHT 19


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
EV	70		0	RELEASE 96-7922-026	5/23/96	SJM LAH
			01	REMOVED PROPOSED DESIGN LABEL	6/26/96	SJM SJM
			A	REV PER 0B20-0491-97	5-6-97	DKE MT
			B	REV PER 0B20-0515-99	18JUN99	MM LW


- 1 MATERIAL:
FRONT AND REAR SHELLS- STEEL.
HOUSING- UL 94V-0 RATED THERMOPLASTIC, BLACK.
OVERMOLD - PVC, COLOR: FROST WHITE.
- 2 FINISH:
FRONT AND REAR SHELLS - TIN PLATED.
3. FINAL CABLE ASSEMBLY LENGTH LONGER THEN 5200mm
EXCEEDS MAX LENGTH @ MAX CONDITIONS PER
UNIVERSAL SERIAL BUS SPEC PARAGRAPH 6.4.



P1




P2



WIRING DIAGRAM			
P1	WIRE COLOR	P2	AWG
1	RED	1	20
2	WHITE	2	28
3	GREEN	3	28
4	BLACK	4	20
SHELL	SHIELD	SHELL	-

5200 ⁺⁰ ₋₇₅	621776-4
5000 ⁺⁰ ₋₇₅	621776-3
4000 ⁺⁰ ₋₇₅	621776-2
3000 ⁺⁰ ₋₅₀	621776-1
A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	S. J. MAGARO	5/23/96	AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK	L. A. HUFF	5/23/96			
		APVD	S. J. MAGARO	5/23/96			
		DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME
mm		PRODUCT SPEC			CABLE ASSEMBLY, 4 POSN USB PLUG, TYPE A TO B, 28/20 AWG		
		APPLICATION SPEC			SIZECAGE CODEDRAWING NO		
0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		- - - - - - -					
MATERIAL		WEIGHT			A200779C=621776		
		-			SCALE2:1		
		CUSTOMER DRAWING			SHEET1 OF 1REV B		