




NO.	ITEM	SPECIFICATION
1	Rated Voltage	6 VDC
2	Direction of Rotation	CCW
3	No Load Current	0.05A max
4	No Load Speed	3 RPM $\pm$ 12%
5	Gear Ratio	340:1
6	Rated Load	2.5 Kg.cm
7	Rated Current	0.09A max
8	Rated Speed	2 RPM $\pm$ 10%
9	Stall Torque	7.35 Kg.cm
10	Stall Current	0.07 A max

Rev.	Revision	Date
01	Update	9/20/2011



DRAWN	Emily	9/20/2011	UNIT: mm		
CHECKED	Sara	9/20/2011			
ENG APPR.					
MFG APPR.			Sinotech		
Q.A.					
B32-6V3.1RPM			SIZE A4	P/N 2146505	REV 01
			SCALE: 2:1	Weight(kg): 0.5	SHEET 1 OF 1