



Endless cable ties with separate head and spacer

- EL-TY-Series

Features and Benefits

Manufactured from very strong Acetal (POM) the system consists of a continuous strap, spacers, and heads (which have stainless steel pawls). Once applied the tie offers a very secure fixing and offers good resistance to ageing and sunlight.


The flexibility of the system allows for minimal stock holding of components as the system can be used to suit any bundle diameter.

Application


These robust cable ties are particularly suitable for use with larger diameter cables, pipes and hoses. Designed originally for securing overhead, catenary, cables (when used with the spacers) they are now used in many industries from the building sector, through to the chemical industry, to the installation of signs for traffic management.



The EL-Ty can be cut to suit any bundle.



Spacer.



Material Data

Material Head	Polyacetal (POMUV; ST) with stainless steel pawl UV-resistant
Cable Tie	Polyacetal (POMUV), UV-weather resistant
Material Spacer	Polypropylene, UV-resistant (PP)
Colour	Black (BK)
Operating Temperature	-40 °C to +85 °C
Flammability	UL94 HB



For detailed information on Application Tools please refer to page 564.

Technical Table

Article-No.	Type	Min. Tensile Strength (N)	Material	Colour	Application Tool	Pack Cont.
111-30000	TELS	1111	POM	Black (BK)	MK9HT	15m strap, 30 heads
111-31000	TELS	1111	POM	Black (BK)	MK9HT	25
111-32000	TELS	—	PP	Black (BK)	-	50

All dimensions in mm. Subject to technical changes.