







- 1 FOR USE WITH .093 MINIMUM THICK PRINTED CIRCUIT BOARD. REFER TO APPLICATION SPECIFICATION FOR PRINTED CIRCUIT BOARD LAYOUT DIMENSIONS AND FINISH RECOMMENDATIONS.
- 2 MOLDED PARTS: FLAME RETARDANT 94V-0 RATED GLASS FILLED, NYLON OR POLYESTER, COLOR: BLACK.
- 3 CONTACTS: COPPER ALLOY.
- 4 SHELL: CARBON STEEL.
- 5 HARDWARE: ZINC ALLOY
- 6 HARDWARE: SCREWLOCKS: CLEAR TRIVALENT CHROMATE COATING.
- 7 SHELL: BRIGHT TIN PLATED.
- 8 GOLD FLASH IN MATING AREA.
.000100 MINIMUM TIN OR TIN-LEAD ON COMPLIANT PIN.
ALL OVER .000050 MINIMUM NICKEL.
- 9 .000030 MIN GOLD IN MATING AREA.
.000100 MIN TIN OR TIN-LEAD ON COMPLIANT PIN.
ALL OVER .000050 MIN NICKEL.
OR
GOLD FLASH OVER PALLADIUM NICKEL.
.000030 MIN TOTAL IN MATING AREA.
.000100 MIN TIN OR TIN-LEAD ON COMPLIANT PIN.
ALL OVER .000050 MIN NICKEL.

		745928-2
OBSOLETE		745928-1
	CONTACT FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN EN ISO 9001:2015 EN 1090-1:2009 EN 1090-2:2009		5-31-88 6-1-88		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		CW 3/16" LENKER CW 3/8" WELDON APWD -		NAME	
		0 PLOC ± - 1 PLOC ± - 2 PLOC ± - 3 PLOC ± .005 4 PLOC ± - 5 ANGLES ± 2° FINISH		PRODUCT SPEC 108-40014 APPLICATION SPEC 114-40026 		RECEPTACLE ASSEMBLY, SIZE 3, 25 POSITION, WITH ACTION PIN CONTACTS, #4-0 SCREWLOCKS, FRONT METAL SHELL, MEDIUM PROFILE,	
MATERIAL				WEIGHT -		SIZE CASE CODE DRAWING NO A1 00779 C=745928	
				CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV S	