


© COPYRIGHT OXLEY DEVELOPMENTS Co. Ltd. 2001



MATERIALS AND FINISHES	
DESCRIPTION	MATERIAL, FINISH
BODY	ALUMINIUM ALLOY, MATT BLACK ANODISED
LENS	POLYCARBONATE
TERMINATIONS	FLYING LEADS : COLOUR RED AND BLACK WIRE INSULATION. LENGTH DEFINED IN PART No. (cm)
NUT	ALUMINIUM ALLOY
WASHER	BeCu. TIN PLATED

ELECTRICAL / OPTICAL CHARACTERISTICS

Electrical / Optical Characteristics	AlGaAs RED	YELLOW	GREEN	BLUE	WHITE
LUMINOUS INTENSITY TYPICAL (mcd AT RATED VOLTAGE)	1200	1000	1250	1200	1000
WAVELENGTH TYPICAL (nm)	637	585	525	470	N/A
FORWARD CURRENT (mA) TYP	20	20	20	20	20
FORWARD VOLTAGE (V)	1.9	1.9	3.6	3.6	3.6
REVERSE VOLTAGE (V) MAX	5				

MOUNTING DETAILS

MOUNTING HOLE : $\phi 10.15 \pm 0.1$
RECOMMENDED MOUNTING
TORQUE : 1Nm
CHASSIS THICKNESS :
1.5mm (Min)

ORDERING INFORMATION :

WHEN ORDERING, STATE TYPE NUMBER, SPECIFYING FLYING LEAD LENGTH AND LED COLOUR

e.g OXL/CLH/100/FL10/G

FLYING LEAD LENGTH IN cm

- COLOUR (AL, Y, G, B or W)

AlGaAs RED, RED, YELLOW, GREEN, BLUE or WHITE