




LOC		DIST		REVISIONS					
GP	00	P	LYR	DESCRIPTION	DATE	OWN	APVD		
		B2		REVISED PER ECO-11-004835	11MAR2011	RK	HMR		



1888019-2
SHOWN WITHOUT PICK AND PLACE DEVICE
SCALE 8:1



1888019-4
SHOWN WITHOUT PICK AND PLACE DEVICE
SCALE 8:1



1888019-8
SHOWN WITHOUT PICK AND PLACE DEVICE
SCALE 8:1

1 MATERIAL: LCP, BLACK.

2 MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.

3 FINISH: 0.76µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.


4 MATERIAL: NICKEL-SILVER PER ASTM B 122.

5 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.

6. REFER TO CUSTOMER DRAWING 1761987 FOR CONNECTOR DETAILS.

7. PACKAGED IN TAPE AND REEL PER EIA-481.


8 FINISH: 0.38µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.



1888019-6
SHOWN WITHOUT PICK AND PLACE DEVICE
SCALE 8:1

8	THRU HOLE	3.5	17.8	16	16	36	18.05	36	1-1888019-2
	THRU HOLE	2.8	17.8	16	16	36	18.05	36	1-1888019-1
	PRESS FIT	-	17.8	16	16	36	18.05	36	1-1888019-0
	THRU HOLE	2	17.8	16	16	36	18.05	36	1888019-9
3	THRU HOLE	3.5	17.8	16	16	36	18.05	36	1888019-8
	THRU HOLE	2.8	17.8	16	16	36	18.05	36	1888019-6
	PRESS FIT	-	17.8	16	16	36	18.05	36	1888019-4
	THRU HOLE	2	17.8	16	16	36	18.05	36	1888019-2
FINISH	SHELL TYPE	G	E	D	C	B	A	POSN	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN	M.E. COWHER	18JUL2005	TE Connectivity		
				CHK	R.R. HENRY	18JUL2005			
				APVD	R.R. HENRY	18JUL2005	NAME		
DIMENSIONS:							EVERCLEAR Mini-SAS RIGHT ANGLE INTERNAL RECEPTACLE ASSEMBLY WITH DUAL KEYED SHELL		
mm							SIZE		
							CAGE CODE		
							DRAWING NO		
							RESTRICTED TO		
							A100779		
							C=1888019		
							SCALE		
							8:1		
							SHEET		
							1		
							OF		
							3		
							REV		
							B2		




LOC		DIST		REVISONS			
GP	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.E. COWHER 18JUL2005	 TE Connectivity	
DIMENSIONS: mm		CHK R.R. HENRY 18JUL2005		
		APVD R.R. HENRY 18JUL2005	NAME EVERCLEAR Mini-SAS RIGHT ANGLE INTERNAL RECEPTACLE ASSEMBLY WITH DUAL KEYED SHELL	
		PRODUCT SPEC 108-2234	SIZE A100779	
MATERIAL SEE NOTES		FINISH SEE TABLE	WEIGHT -	
		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE 8:1		SHEET 2 OF 3
				REV B2

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	OWN	APVD
				-	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN M.E. COWHER	18JUL2005	 TE Connectivity	
		CHK R.R. HENRY	18JUL2005		
DIMENSIONS:		APVD R.R. HENRY	18JUL2005	NAME	
mm		PRODUCT SPEC		EVERCLEAR Mini-SAS RIGHT ANGLE INTERNAL RECEPTACLE ASSEMBLY WITH DUAL KEYED SHELL	
		APPLICATION SPEC		SIZE	
		-		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
SEE NOTES		-		A100779C-1888019	
FINISH		CUSTOMER DRAWING		RESTRICTED TO	
SEE TABLE				-	
		SCALE		SHEET	
		8:1		3 OF 3	
				REV	
				B2	