



PANDUIT PART NO.	MAX BUNDLE DIA.	PACKAGE QTY	LENGTH "L" ±.3 [7]
MLT2.7WS-LP	2.7" [69]	50	10.2" [259]
MLT4WS-LP	4" [102]	50	14.3" [362]
MLT6WS-LP	6" [152]	50	20.5" [521]
MLT8WS-LP	8" [203]	50	20.8" [679]
MLT4WS-TL	4" [102]	250	14.3" [362]




1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH -
200 LBS (890 NEWTONS) WHEN TESTED ON A 3" MANDREL.
PART NO.MLT2.7WS-LP TESTED ON A 1 1/2" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE
SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = $\pm .010$ [.25] .XX = $\pm .02$ [.5]
.X = $\pm .03$ [.8] ANGLES = $\pm 2^\circ$
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY



10A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
09A	1/13	JAMB	RGRO	---	ADDED PART NUMBER MLT4WS-TL TO DRAWING	-----
08A	2/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE						WAVE-TY STANDARD SERIES 304 STAINLESS STEEL	
ITEM REVISION NAME						CUSTOMER DRAWING	
N41124BS/10							
DATASET FILE NAME							
N41124BS_DC/10A						MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						304 STAINLESS STEEL	
.x ± .1 [2.54] .xxx ± .005 [.127]						DRAWING NUMBER: N41124BS_DC	
.xx ± .01 [.25] ANGLES ± 5 °							
						THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE	SIZE			
JAMB	02/12	DPN	2:1	SHT 1 OF 1			
				A			