


Capacitor, Tantalum, Military (non-ER) Radial Conformal (Dipped), 22 uF, +/-20% Tol, 50 V



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	10.16	
H	18.80	
F	0.51	+/-0.05
S	6.35	+/-0.38
LL	4.75	+/-0.81

General Information	
Supplier:	KEMET
Application:	Military/General Purpose
Part Type Description:	Military (non-ER) Radial Conformal (Dipped)
Body Type:	Radial Conformal (Dipped)
Lead Type:	Formed Out
Termination Type:	Tin-Lead (SnPb)

Specifications	
Capacitance:	22 uF
Tolerance:	+/-20%
Voltage:	50 V (85C)
Voltage:	65 V (85C Surge)
Voltage:	2.5 V (85C Reverse)
Temperature Range:	-55/+85C
Leakage Current:	8.8 uA
Dissipation Factor:	6%

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.