

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

BELDEN
SENDING ALL THE RIGHT SIGNALS

673948 Coax - CCTV Applications



For more Information
please call

1-800-Belden1



General Description:

Surveillance & CCTV Cable, mini-RG59, Plenum-CMP, 25 AWG solid bare copper, foamed FEP core, 95% bare copper braid, Flamarrest® jacket

Usage (Overall)

Suitable Applications:	Analog Video, CCTV
------------------------	--------------------

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	25	Solid	BC - Bare Copper	.018

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FFEP - Foam Fluorinated Ethylene Propylene	.078

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter:	0.146 in.
---------------------------	-----------

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
------------------------------	----------------

UL Temperature Rating:	75°C
------------------------	------

Bulk Cable Weight:	17 lbs/1000 ft.
--------------------	-----------------

Max. Recommended Pulling Tension:	28 lbs.
-----------------------------------	---------

Min. Bend Radius/Minor Axis:	1.500 in.
------------------------------	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
-------------------------	-----

NEC Articles:	800
---------------	-----

CEC/C(UL) Specification:	CMP
--------------------------	-----

EU Directive 2011/65/EU (ROHS II):	Yes
------------------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	12/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

673948 Coax - CCTV Applications

RG Type:	Mini 59/U
Series Type:	Series 59
Flame Test	
UL Flame Test:	NFPA 262
CSA Flame Test:	FT6
Suitability	
Suitability - Indoor:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	Yes

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (μH/ft)
.109

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.9

Nominal Velocity of Propagation:

VP (%)
80

Nominal Delay:

Delay (ns/ft)
1.27

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
31.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.5

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.45
5	.90
10	1.3
50	3.1
100	4.3
200	6.3
400	9.4
700	13.0
900	15.0
1000	16.0

Max. Operating Voltage - UL:

Voltage
300 V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
673948 877U500	500 FT	9.000 LB	NATURAL		#25 FPFA BRD PVC
673948 8771000	1,000 FT	17.000 LB	NATURAL		#25 FPFA BRD PVC

Revision Number: 1 Revision Date: 03-11-2013

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



673948 Coax - CCTV Applications

safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.