




(2,00 mm) .0787"

TSH, TMMS SERIES

SHROUDED HEADERS

Mates with:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS, PTF

SPECIFICATIONS

For complete specifications and
recommended PCB layouts
see www.samtec.com/TSH**Insulator Material:**
Black Liquid Crystal Polymer**Terminal Material:**

Phosphor Bronze

Plating:

Sn or Au over
50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant: Yes

Processing:

Lead-Free Solderable: Yes

SMT Lead Coplanarity:

(0,15 mm) .006" max

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality

FILE NO. E111594

Note: Some lengths, styles
and options are non-standard,
non-returnable.

TSH	1	NO. PINS PER ROW	01	PLATING OPTION	ROW OPTION	OTHER OPTION
05, 10, 15, 20, 25, 30, 35, 40, 45 (40 & 45 = -D & -RA only) (Standard sizes)			-F = Gold flash on post, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail -T = Matte Tin		-D = Vertical Through-Hole -DV = Vertical Surface Mount -RA = Right Angle Through-Hole -DH = Horizontal Surface Mount	-LC = Locking Clip (-DV only) (N/A with -A) (Manual placement required) -A = Alignment Pin (-DV only) (N/A with -LC) -SL = Solder Locks (-DH only) -K = (4,50 mm) .177" DIA Polyimide Film Pick & Place Pad (N/A with 15 - 30 positions) (-DH only) -M = Metal Pick & Place Pad (-DV only) (N/A -T plating) -TR = Tape & Reel

ALSO AVAILABLE
(MOQ Required)

- Other sizes and platings
Contact Samtec.

Mates with:
SQT, SQW, ESQT

SPECIFICATIONS

For complete specifications
see www.samtec.com/TMMS**Insulator Material:**

Black LCP

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over

50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Lead-Free Solderable: Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality

FILE NO. E111594

Note: Some lengths, styles
and options are non-standard,
non-returnable.

TMMS	1	NO. PINS PER ROW	01	PLATING OPTION	Q	OPTION	FS
05, 10, 15, 20, 30, 40, 50			-F = Gold flash on post, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail		-RA = Right Angle		

4 ROW

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685