





Rev	AWO #	Description	Date	Appr
-		RELEASED	3/29/05	
A		UPDATED	12/10/07	
B		ADDED CENTER BAR	3/9/10	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Insulator: PBT, Glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 1 Amp max
Contact resistance: 20 mohms max initial
Insulation resistance: 5,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Operating temperature: -55°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 20, 24, 26, 28, 32, 40, 42, & 48
A = .100 [2.54] x No. of Positions Per Row
B = .100 [2.54] x No. of Spoces Per Row

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE IC SOCKET, .600" ROW SPACING
TIN PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				DATE			
.X	± .10	ØX	± .10	SS	3/29/05	SIZE	PART NO.
.XX	± .020	ØXX	± .015	CHECKED		X	ICS-6XX-T
.XXX	± .015	ØXXX	± .010	APPROVED		REF:	SCALE: NTS
APPROVALS							SHEET 1 OF 1

