

## DM74ALS373

### Octal D-Type 3-STATE Transparent Latch

#### General Description

These 8-bit registers feature totem-pole 3-STATE outputs designed specifically for driving highly-capacitive or relatively low-impedance loads. The high-impedance state and increased high-logic-level drive provide these registers with the capability of being connected directly to and driving the bus lines in a bus-organized system without need for interface or pull-up components. They are particularly attractive for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers.

The eight latches of the DM74ALS373 are transparent D-type latches. While the enable (G) is HIGH the Q outputs will follow the data (D) inputs. When the enable is taken LOW the output will be latched at the level of the data that was set up.

A buffered output control input can be used to place the eight outputs in either a normal logic state (HIGH or LOW logic levels) or a high-impedance state. In the high-impedance state the outputs neither load nor drive the bus lines significantly.

The output control does not affect the internal operation of the latches. That is, the old data can be retained or new data can be entered even while the outputs are OFF.

#### Features


- Switching specifications at 50 pF
- Switching specifications guaranteed over full temperature and  $V_{CC}$  range
- Advanced oxide-isolated, ion-implanted Schottky TTL process
- Functionally and pin for pin compatible with LS TTL counterpart
- Improved AC performance over DM74LS373 at approximately half the power
- 3-STATE buffer-type outputs drive bus lines directly

#### Ordering Code:

| Order Number | Package Number | Package Description                                                       |
|--------------|----------------|---------------------------------------------------------------------------|
| DM74ALS373WM | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300 Wide |
| DM74ALS373SJ | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide             |
| DM74ALS373N  | N20A           | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300 Wide     |

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### Connection Diagram




DM74ALS373 Octal D-Type 3-STATE Transparent Latch

## Function Table

| Output<br>Control | Enable<br>G | D | Output<br>Q    |
|-------------------|-------------|---|----------------|
| L                 | H           | H | H              |
| L                 | H           | L | L              |
| L                 | L           | X | Q <sub>0</sub> |
| H                 | X           | X | Z              |

L = LOW State  
H = HIGH State  
X = Don't Care  
Z = High Impedance State  
 $Q_0$  = Previous Condition of Q

### Logic Diagram



**Absolute Maximum Ratings**(Note 1)

|                                      |                 |
|--------------------------------------|-----------------|
| Supply Voltage                       | 7V              |
| Input Voltage                        | 7V              |
| Voltage Applied to Disabled Output   | 5.5V            |
| Operating Free Air Temperature Range | 0°C to +70°C    |
| Storage Temperature Range            | –65°C to +150°C |
| Typical $\theta_{JA}$                |                 |
| N Package                            | 57.0°C/W        |
| M Package                            | 76.0°C/W        |

**Note 1:** The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

**Recommended Operating Conditions**

| Symbol   | Parameter                          | Min | Nom | Max  | Units |
|----------|------------------------------------|-----|-----|------|-------|
| $V_{CC}$ | Supply Voltage                     | 4.5 | 5   | 5.5  | V     |
| $V_{IH}$ | HIGH Level Input Voltage           | 2   |     |      | V     |
| $V_{IL}$ | LOW Level Input Voltage            |     |     | 0.8  | V     |
| $I_{OH}$ | HIGH Level Output Current          |     |     | –2.6 | mA    |
| $I_{OL}$ | LOW Level Output Current           |     |     | 24   | mA    |
| $t_W$    | Width of Enable Pulse, HIGH or LOW | 10  |     |      | ns    |
| $t_{SU}$ | Data Setup Time (Note 2)           | 10↓ |     |      | ns    |
| $t_H$    | Data Hold Time (Note 2)            | 7↓  |     |      | ns    |
| $T_A$    | Free Air Operating Temperature     | 0   |     | 70   | °C    |

**Note 2:** The (↓) arrow indicates the negative edge of the enable is used for reference.

**Electrical Characteristics**

over recommended operating free air temperature range. All typical values are measured at  $V_{CC} = 5V$ ,  $T_A = 25^\circ C$ .


| Symbol    | Parameter                                              | Conditions                                               | Min              | Typ  | Max  | Units   |
|-----------|--------------------------------------------------------|----------------------------------------------------------|------------------|------|------|---------|
| $V_{IK}$  | Input Clamp Voltage                                    | $V_{CC} = 4.5V$ , $I_I = -18\text{ mA}$                  |                  |      | –1.5 | V       |
| $V_{OH}$  | HIGH Level Output Voltage                              | $V_{CC} = 4.5V$ , $I_{OH} = -2.6\text{ mA}$              | 2.4              | 3.3  |      | V       |
|           |                                                        | $V_{CC} = 4.5V$ to $5.5V$ , $I_{OH} = -400\text{ }\mu A$ | $V_{CC} - 2$     |      |      | V       |
| $V_{OL}$  | LOW Level Output Voltage                               | $V_{CC} = 4.5V$ , $I_{OL} = 24\text{ mA}$                |                  | 0.35 | 0.5  | V       |
| $I_I$     | Input Current at Maximum Input Voltage                 | $V_{CC} = 5.5V$ , $V_{IH} = 7V$                          |                  |      | 0.1  | mA      |
| $I_{IH}$  | HIGH Level Input Current                               | $V_{CC} = 5.5V$ , $V_{IH} = 2.7V$                        |                  |      | 20   | $\mu A$ |
| $I_{IL}$  | LOW Level Input Current                                | $V_{CC} = 5.5V$ , $V_{IL} = 0.4V$                        |                  |      | –0.1 | mA      |
| $I_O$     | Output Drive Current                                   | $V_{CC} = 5.5V$ , $V_O = 2.25V$                          | –30              |      | –112 | mA      |
| $I_{OZH}$ | OFF-State Output Current<br>HIGH Level Voltage Applied | $V_{CC} = 5.5V$ , $V_O = 2.7V$                           |                  |      | 20   | $\mu A$ |
| $I_{OZL}$ | OFF-State Output Current<br>LOW Level Voltage Applied  | $V_{CC} = 5.5V$ , $V_O = 0.4V$                           |                  |      | –20  | $\mu A$ |
| $I_{CC}$  | Supply Current                                         | $V_{CC} = 5.5V$ , Outputs OPEN                           | Outputs HIGH     | 9    | 16   | mA      |
|           |                                                        |                                                          | Outputs LOW      | 16   | 25   | mA      |
|           |                                                        |                                                          | Outputs Disabled | 17   | 27   | mA      |

## Switching Characteristics

over recommended operating free air temperature range


| Symbol    | Parameter                                          | Conditions                                                      | From              | To    | Min | Max | Units |
|-----------|----------------------------------------------------|-----------------------------------------------------------------|-------------------|-------|-----|-----|-------|
| $t_{PLH}$ | Propagation Delay Time<br>LOW-to-HIGH Level Output | $V_{CC} = 4.5V$ to $5.5V$<br>$R_L = 500\Omega$<br>$C_L = 50$ pF | Data              | Any Q | 2   | 12  | ns    |
| $t_{PHL}$ | Propagation Delay Time<br>HIGH-to-LOW Level Output |                                                                 | Data              | Any Q | 4   | 16  | ns    |
| $t_{PLH}$ | Propagation Delay Time<br>LOW-to-HIGH Level Output |                                                                 | Enable            | Any Q | 6   | 22  | ns    |
| $t_{PHL}$ | Propagation Delay Time<br>HIGH-to-LOW Level Output |                                                                 | Enable            | Any Q | 7   | 23  | ns    |
| $t_{PZH}$ | Output Enable Time<br>to HIGH Level Output         |                                                                 | Output<br>Control | Any Q | 6   | 18  | ns    |
| $t_{PZL}$ | Output Enable Time<br>to LOW Level Output          |                                                                 | Output<br>Control | Any Q | 5   | 20  | ns    |
| $t_{PHZ}$ | Output Disable Time<br>from HIGH Level Output      |                                                                 | Output<br>Control | Any Q | 2   | 10  | ns    |
| $t_{PLZ}$ | Output Disable Time<br>from LOW Level Output       |                                                                 | Output<br>Control | Any Q | 2   | 12  | ns    |

**Physical Dimensions** inches (millimeters) unless otherwise noted




**20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300 Wide  
Package Number M20B**


# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



## LAND PATTERN RECOMMENDATION




DIMENSIONS ARE IN MILLIMETERS



## NOTES:

- A. CONFORMS TO EIAJ EDR-7320 REGISTRATION, ESTABLISHED IN DECEMBER, 1998.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.


M20DRevB1



## DETAIL A

20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide  
Package Number M20D

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300 Wide  
Package Number N20A

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)