







- ① MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- ② FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- ③ FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- ⑤ FOR GROUNDED GUIDE PIN USE $\varnothing 3.56 \pm 0.08$ PTH,
 $\varnothing 3.66$ DRILL, AND $\varnothing 6.5$ PAD.
6. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.



RIGHT GUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.										DWN		K. SHOBER		13JAN2011				TE Connectivity							
DIMENSIONS: mm										CHE		EABY		13JAN2011											
																				APOB		FABY		13JAN2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 2 PLC ±0.13 2 PLC ± 2 PLC ± ANGLES ±°																				PRODUCT SPEC				SIZE	
										MATERIAL 										APPLICATION SPEC					
FINISH SEE TABLE																				WEIGHT		-		A100779C	
										CUSTOMER DRAWING															
																				SCALE		6:1		SHEET	

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-

	H	5.5	8-2007815-6
	H	4.9	8-2007815-5
	H	4.5	8-2007815-4
	H	5.5	8-2007815-3
	H	4.9	8-2007815-2
	H	4.5	8-2007815-1
	G	5.5	7-2007815-6
	G	4.9	7-2007815-5
	G	4.5	7-2007815-4
	G	5.5	7-2007815-3
	G	4.9	7-2007815-2
	G	4.5	7-2007815-1
	F	5.5	6-2007815-6
	F	4.9	6-2007815-5
	F	4.5	6-2007815-4
	F	5.5	6-2007815-3
	F	4.9	6-2007815-2
	F	4.5	6-2007815-1
	E	5.5	5-2007815-6
	E	4.9	5-2007815-5
	E	4.5	5-2007815-4
	E	5.5	5-2007815-3
	E	4.9	5-2007815-2
	E	4.5	5-2007815-1
	D	5.5	4-2007815-6
	D	4.9	4-2007815-5
	D	4.5	4-2007815-4
	D	5.5	4-2007815-3
	D	4.9	4-2007815-2
	D	4.5	4-2007815-1
	C	5.5	3-2007815-6
	C	4.9	3-2007815-5
	C	4.5	3-2007815-4
	C	5.5	3-2007815-3
	C	4.9	3-2007815-2
	C	4.5	3-2007815-1
	B	5.5	2-2007815-6
	B	4.9	2-2007815-5
	B	4.5	2-2007815-4
	B	5.5	2-2007815-3
	B	4.9	2-2007815-2
	B	4.5	2-2007815-1
	A	5.5	1-2007815-6
	A	4.9	1-2007815-5
	A	4.5	1-2007815-4
	A	5.5	1-2007815-3
	A	4.9	1-2007815-2
	A	4.5	1-2007815-1
	-	5.5	2007815-6
	-	4.9	2007815-5
	-	4.5	2007815-4
	-	5.5	2007815-3
	-	4.9	2007815-2
	-	4.5	2007815-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. K. SHOBER	13JAN2011	TE Connectivity		
			CHK	J. EABY	13JAN2011			
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	IMPACT, 4 PAIR, 10 COLUMN, HEADER RIGHT GUIDED, LEFT END WALL SIGNAL MODULE, 0.36 PTH	
mm						PRODUCT SPEC		
			9 PLC	±		APPLICATION SPEC	SIZE	CAGE CODE
			3 PLC	±0.25			DRAWING NO	RESTRICTED TO
			5 PLC	±0.13			A100779	C=2007815
			4 PLC	±				
MATERIAL			FINISH	SEE TABLE		WEIGHT	-	
-						CUSTOMER DRAWING	SCALE	5:1
							SHEET	2
							OF	2
							REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2007815-1](#)