

T1/E1/CEPT/ISDN-PRI TRANSFORMERS

Reinforced Insulation, 3 kVrms, SMT



Pulse

A TECHNITROL COMPANY



- RoHS-6 peak reflow temperature rating: 245°C
- Dual surface mount package contains both transmit and receive transformers
- Models matched to leading transceiver ICs
- 3 kV reinforced insulation barrier approved to UL

3 kV
Reinforced!



Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C

RoHS-6 Compliant Part Number	Turns Ratio (Pri:Sec ±2%)	OCL @ 25°C (mH MIN)	C _{w/w} (pF MAX)	DCR Pri (Ω MAX)	DCR Sec (Ω MAX)	Package/Schematic	Primary Pins
T1030NL	1CT:1CT & 1CT:1CT	1.20 & 1.20	15 & 15	1.00 & 1.00	1.00 & 1w.00	ZIN / 1	1-3, 6-8
T1035NL	1CS:1CS & 1CS:1.36CS	1.20 & 1.20	15 & 15	1.00 & 1.00	1.00 & 1.20	ZIN / 2	1-4, 5-8
T1038NL	1CT:1CT & 1CT:1.36CT	1.20 & 1.20	15 & 15	1.00 & 1.00	0.90 & 1.20	ZIN /1	1-3, 6-8


Mechanical

Schematics

ZIN



SUGGESTED PAD LAYOUT



1

2

Weight 8.1 grams
Tube 20/tube
Tray 250/tray

Dimensions: Inches
mm
Unless otherwise specified, all tolerances are \pm 0.010
0.26

T1/E1/CEPT/ISDN-PRI TRANSFORMERS

Reinforced Insulation, 3 kVrms, SMT




Application Notes

1. Safety Standards Recognition

All transformers listed on this data sheet are UL1459, UL1950, CS950 approved per Underwriters Laboratories – file E133523, Reinforced Insulation.

2. Crosstalk Attenuation

The dual packages contain transmit and receive transformers side by side, sufficient crosstalk attenuation is achieved by the inherent characteristics of the toroid cores as well as by their proper positioning. The crosstalk attenuation is typically 55 dB or better from 100 kHz to 10 MHz. This result was established with the test circuit shown here:



3. Common Mode Chokes

The "high-frequency" 4-line common mode chokes, in the chart below, provide an effective means of compliance with national and international regulations on EMI. They are designed to be used in conjunction with Pulse's T1/CEPT transformers. Crosstalk is typically – 70 dB at 1 MHz and – 55 dB at 10 MHz.

High Frequency Common Mode Chokes for Telecom Applications (4-Lines)

Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C							
Pulse Part Number	Turns Ratio (±5%)	OCL (µH MIN)	C _{w/w} (pF MAX)	L _L (µH MAX)	DCR (Ω MAX)	Isolation (Vrms MIN)	Package
PE-65554NL	1:1:1:1	24.0	15	.20	0.30	500	Through Hole
PE-65555NL	1:1:1:1	8.0	10	.20	0.25	500	Through Hole
PE-65854NL	1:1:1:1	47.0	16	.20	0.30	500	Surface Mount
PE-65857NL	1:1:1:1	24.0	15	.23	0.30	500	Surface Mount

Note: Additional common mode chokes to improve EMI performance are available. See the "Common Mode Choke Catalog," for mechanicals and schematics on the data sheet menu on the pulse web site: <http://www.pulseeng.com/index.php?848>, under "Pulse Catalog and General Catalogs."

For More Information:

Pulse Worldwide Headquarters	Pulse Europe	Pulse China Headquarters	Pulse North China	Pulse South Asia	Pulse North Asia
12220 World Trade Dr. San Diego, CA 92128 U.S.A.	Einsteinstrasse 1 D-71083 Herrenberg Germany	B402, Shenzhen Academy of Aerospace Technology Bldg. 10th Kejinan Rd. High-Tech Zone Nanshan District Shenzhen, PR China 518057	Room 1503 XinYin Building No. 888 YiShan Rd. Shanghai 200233 China	135 Joo Seng Rd. #03-02 PM Industrial Bldg. Singapore 368363	No. 26, Kao Ching Rd. Yang Mei Chen Taoyuan Hsien Taiwan R. O. C.
www.pulseeng.com	Tel: 858 674 8100 Fax: 858 674 8262	Tel: 49 7032 7806 0 Fax: 49 7032 7806 135	TEL: 86 755 33966678 FAX: 86 755 33966700	Tel: 86 21 54643211/2 Fax: 86 21 54643210	TEL: 65 6287 8998 FAX: 65 6280 0080
					Tel: 886 3 4643715 Fax: 886 3 4641911

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

© Copyright, 2009. Pulse Engineering, Inc. All rights reserved.