

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
				B2		REV PER ECR 07-030318	14DEC07	JR	TM
AMP WIRE RANGE 8 AWG STRANDED									
13.8 [.543] MAX WASHER R DIMPLED SURFACE INSULATION 5.2±0.08 [.205±.003] DIA FOR M5 STUD 10.9 [.430] 29.8 [1.173] MAX 35.26 [1.388] MAX				1 TONGUE MATERIAL THK IS 1.02±0.08 [.040±.003]. 2 FOR 6.50 [.256] MAX WIRE INS. DIA 3 MATERIAL: BODY - COPPER PER ASTM B152 SLEEVE - NYLON 4 FINISH: BODY - TIN PLATE PER ASTM B545 SLEEVE - COLOR - RED					
				100		LOOSE PIECE		130703	
				QTY		PACKAGING TYPE		PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS				MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		THIS DRAWING IS A CONTROLLED DOCUMENT.			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 MAX		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 6.64-10.5mm² [31,100-20,900] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± 5°		FINISH	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL		-3	
								-4	
						DWN jr ruth 21AUG07 CHK T MICHELUTTI 21AUG07 APVD T MICHELUTTI 21AUG07 PRODUCT SPEC APPLICATION SPEC WEIGHT -		Tyco Electronics Corporation Harrisburg, PA 17105-3608 NAME TERMINAL, RING TONGUE, TERMINYL, WIRE SIZE: 8 AWG SIZE A3 CAGE CODE 00779 DRAWING NO C-130703 RESTRICTED TO -	
						CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV B2	