




Agilent 33210A 10 MHz Function/Arbitrary Waveform Generator

Data Sheet

- 10 MHz Sine and Square waveforms
- Pulse, Ramp, Triangle, Noise, and DC waveforms
- Optional 14-bit, 50 MSa/s, 8K point Arbitrary Waveform Generator
- AM, FM, and PWM modulation types
- Linear & logarithmic sweeps and burst operation
- 10 mVpp to 10 Vpp amplitude range
- Graph mode for visual verification of signal settings
- Connect via USB, GPIB and LAN
- Fully compliant to LXI Class C specification



Uncompromising performance at an affordable price

The Agilent Technologies 33210A function/arbitrary waveform generator is the latest addition to the 332XX family. Waveforms are generated using direct digital synthesis (DDS) technology which creates stable, accurate low distortion sine waves as well as square waves with fast rise and fall times up to 10 MHz and linear ramp waves up to 100 kHz. For user defined waveforms, Option 002 provides 14-bit, 50 MSa/s 8K point arbitrary waveform generation.

Pulse generation

The 33210A can generate variable-edge-time pulses up to 5 MHz. With variable period, pulse width, and amplitude the 33210A is ideally suited to a wide variety of applications requiring a flexible pulse signal.

Custom waveform generation (Option 002)

The optional 8K point arbitrary waveform generator (Option 002) can be used in the 33210A to generate complex custom waveforms. With 14-bit resolution, and a sampling rate of 50 MSa/s, the 33210A gives you the flexibility to create the waveforms you need. It also lets you store up to four waveforms in nonvolatile memory.

The Agilent IntuiLink arbitrary waveform software allows you to easily create, edit, and download complex waveforms using the waveform editor. Or you can capture a waveform using IntuiLink for Oscilloscopes and send it to the 33210A for output. To find out more about IntuiLink, visit

www.agilent.com/find/intuilink



Measurement Characteristics

Easy-to-use functionality

Front-panel operation of the 33210A is straight-forward and user friendly. You can access all major functions with a single key or two. The knob or numeric keypad can be used to adjust frequency, amplitude, offset, and other parameters. You can even enter voltage values directly in Vpp, Vrms, dBm, or as high and low levels. Timing parameters can be entered in Hertz (Hz) or seconds.

Internal AM, FM, and PWM modulation make it easy to modulate waveforms without the need for a separate modulation source. Linear and logarithmic sweeps are also built in, with sweep rates selectable from 1 ms to 500 s. Burst mode operation allows for a user-selected number of cycles per trigger. GPIB, LAN, and USB interfaces are all standard, plus you get full programmability using SCPI commands.

External frequency reference (Option 001)

The 33210A external frequency reference lets you synchronize to an external 10 MHz clock, to another 33210A, or to an Agilent 33220A or Agilent 33250A. Phase adjustments can be made from the front panel or via a computer interface, allowing precise phase calibration and adjustment.

Waveforms

Standard	Sine, Square, Ramp, Triangle, Pulse, Noise, DC
Built-in arbitrary waveforms (available only with Option 002 ARB)	Exponential rise, Exponential fall, Negative ramp, Sin(x)/x, Cardiac

Waveform Characteristics

Sine		
Frequency range	1 mHz to 10 MHz	
Amplitude	(relative to 1 kHz)	
Flatness ^{[1], [2]}	< 100 kHz	0.1 dB
	100 kHz to 5 MHz	0.2 dB
	5 MHz to 10 MHz	0.3 dB

Harmonic distortion ^{[2], [3]}	< 1 Vpp	≥ 1 Vpp
DC to 20 kHz	-70 dBc	-70 dBc
20 kHz to 100 kHz	-65 dBc	-60 dBc
100 kHz to 1 MHz	-50 dBc	-45 dBc
1 MHz to 10 MHz	-40 dBc	-30 dBc

Total harmonic distortion ^{[2], [3]}	DC to 20 kHz	0.04%
---	--------------	-------

Spurious (non-harmonic) ^{[2], [4]}	DC to 1 MHz	-70 dBc
	1 MHz to 10 MHz	-70 dBc + 6 dB/octave

Phase noise (10 kHz offset)	-115 dBc / Hz, typical
-----------------------------	------------------------

Square	
Frequency range	1 mHz to 10 MHz
Rise/fall time	20 ns
Overshoot	< 2%
Variable duty cycle	20% to 80% (to 5 MHz) 40% to 60% (to 10 MHz)

Asymmetry (@ 50% duty)	1% of period + 5 ns
Jitter (RMS)	1 ns + 100 ppm of period

Ramp, Triangle	
Frequency range	1 mHz to 100 kHz
Linearity	< 0.1% of peak output
Variable symmetry	0.0% to 100.0%

Pulse	
Frequency range	1 mHz to 5 MHz
Pulse width (period ≤ 10 s)	40 ns minimum 10 ns resolution
Variable edge time	20 ns to 100 ns
Overshoot	< 2%
Jitter (RMS)	300 ps + 0.1 ppm of period

Noise	
Bandwidth	7 MHz typical

8K-point Arbitrary Waveform Generator (Option 002)

Frequency range	1 mHz to 3 MHz
Waveform length	2 to 8 k points
Amplitude resolution	14 bits (including sign)
Sample rate	50 MSa/s
Min. rise/fall time	70 ns typical
Linearity	< 0.1% of peak output
Settling time	< 500 ns to 0.5% of final value
Jitter (RMS)	6 ns + 30 ppm
Non-volatile memory	4 waveforms

Common Characteristics

Frequency	
Accuracy ^[5]	± (10 ppm + 3 pHz) in 90 days ± (20 ppm + 3 pHz) in 1 year
Resolution	1 μHz (internal) 1 mHz (user)

Amplitude	
Range	10 mVpp to 10 Vpp into 50 Ω 20 mVpp to 20 Vpp into open circuit

Accuracy ^{[1], [2]} (at 1 kHz)	± 2% of setting ± 1 mVpp
Units	Vpp, Vrms, dBm
Resolution	3 digits

DC Offset	
Range (peak AC + DC)	± 5 V into 50 Ω ± 10 V into open circuit
Accuracy ^{[1], [2]}	± 2% of offset setting ± 0.5% of amplitude ± 2 mV
Resolution	3 digits

Main Output	
Impedance	50 Ω typical
Isolation	42 Vpk maximum to earth
Protection	Short-circuit protected, overload automatically disables main output

External Frequency Reference (Option 001)

Rear Panel Input	
Lock range	10 MHz ± 500 Hz
Level	100 mVpp to 5 Vpp
Impedance	1 kΩ, typical
Lock time	< 2 seconds

Rear Panel Output	
Frequency	10 MHz
Level	632 mVpp (0 dBm), typical
Impedance	50 Ω, typical AC coupled

Phase Offset	
Range	+360° to -360°
Resolution	0.001°
Accuracy	20 ns

Measurement Characteristics (Continued)

Modulation

AM

Carrier waveforms	Sine, Square
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb ^[7] (2 mHz to 20 kHz)
Depth	0.0% to 120.0%

FM

Carrier waveforms	Sine, Square
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb ^[7] (2 mHz to 20 kHz)
Deviation	DC to 5 MHz

PWM

Carrier waveforms	Pulse
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb ^[7] (2 mHz to 20 kHz)
Deviation	0% to 100% of pulse width

External Modulation Input

(for AM, FM, PWM)

Voltage range	± 5 V full scale
Input impedance	5 kΩ typical
Bandwidth	DC to 20 kHz

Sweep

Waveforms	Sine, Square, Ramp
Type	Linear or Logarithmic
Direction	Up or Down
Sweep time	1 ms to 500 s
Trigger source	Single, External or Internal
Marker	Falling edge of sync signal (programmable frequency)

Burst ^[6]

Waveforms	Sine, Square, Ramp
Type	Counted (1 to 50,000 cycles), Infinite, Gated
Start/stop phase	+360° to -360°
Internal period	1 μs to 500 s
Gate source	External trigger
Trigger source	Single, External or Internal

Trigger Characteristics

Trigger Input

Input level	TTL compatible
Slope	Rising or Falling, selectable
Pulse width	> 100 ns
Input impedance	> 10 kΩ, DC coupled
Latency	< 500 ns
Jitter (rms)	6 ns (3.5 ns for pulse)

Trigger Output

Level	TTL compatible into ≥ 1 kΩ
Pulse width	> 400 ns
Output impedance	50 Ω typical
Maximum rate	1 MHz
Fanout	≤ 4 Agilent 33210As (or equivalent)

Programming Times (typical)

Configuration times	USB	LAN	GPIO
Function change	120 ms	120 ms	120 ms
Frequency change	2 ms	3 ms	2 ms
Amplitude change	30 ms	30 ms	30 ms
Select user arb	130 ms	130 ms	130 ms
Arb download times (Option 002)	Binary transfer		
	USB	LAN	GPIO
2 k points	5 ms	9 ms	10 ms
4 k points	8 ms	15 ms	20 ms
8 k points	14 ms	27 ms	40 ms

General

Power supply	Cat II 100 – 240 V @ 50/60 Hz (-5%, +10%) 100 – 120 V @ 400 Hz (± 10%)
Power consumption	50 VA max
Operating environment	IEC 61010 Pollution Degree 2 Indoor Location
Operating temperature	0 °C to 55 °C
Operating humidity	5% to 80% RH, non-condensing
Operating altitude	Up to 3000 meters
Storage temperature	-30 °C to 70 °C
State storage memory	Power off state automatically saved, Four user-configurable stored states
Interface	LAN LXI-C Ethernet 10/100 USB 2.0, GPIO
Language	SCPI – 1993, IEEE-488.2
Dimensions (W x H x D)	
Bench top	261.1 mm x 103.8 mm x 303.2 mm
Rack mount	212.88 mm x 88.3 mm x 272.3 mm
Weight	3.4 kg (7.5 lbs)
Safety designed to	UL-1244, CSA 1010 EN61010
EMC tested to	MIL-461C, EN55011, EN50082-1
Vibration and shock	MIL-T-28800, Type III, Class 5
Acoustic noise	30 dBA
Warm-up time	1 hour

Footnotes

- [1] Add 1/10th of output amplitude and offset spec per °C for operation outside the range of 18 °C to 28 °C
- [2] Autorange enabled
- [3] DC offset set to 0 V
- [4] Spurious output at low amplitude is -75 dBm typical
- [5] Add 1 ppm/°C average for operation outside the range of 18 °C to 28 °C
- [6] Sine and square waveforms above 3 MHz are allowed only with an “infinite” burst count
- [7] Only available if Option 002 is installed

Ordering Information

Agilent 33210A

10 MHz function/arbitrary waveform generator

Accessories included

Operating manual, service manual, quick reference guide, IntuiLink waveform editor software, test data, USB cable, and power cord (see language option).

Options

- Opt. 001** External timebase reference
- Opt. 002** 8K-point arbitrary waveform generator
- Opt. A6J** ANSI Z540 calibration
- Opt. AB0** Taiwan: Chinese manual
- Opt. AB1** Korea: Korean manual
- Opt. AB2** China: Chinese manual
- Opt. ABA** English: English manual
- Opt. ABD** Germany: German manual
- Opt. ABF** France: French manual
- Opt. ABJ** Japan: Japanese manual
- Opt. PLG** Continental European power cord

Other Accessories

- 34131A** Carrying case
- 34161A** Accessory pouch
- 34190A** Rackmount kit
- 34191A** Dual flange kit, 2U
- 34194A** Dual lock link kit



Agilent Advantage Services is committed to your success throughout your equipment's lifetime. To keep you competitive, we continually invest in tools and processes that speed up calibration and repair and reduce your cost of ownership. You can also use Infoline Web Services to manage equipment and services more effectively. By sharing our measurement and service expertise, we help you create the products that change our world.

www.agilent.com/find/advantageservices



myAgilent

www.agilent.com/find/myagilent

A personalized view into the information most relevant to you.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Agilent is a founding member of the LXI consortium.

Agilent Channel Partners

www.agilent.com/find/channelpartners

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	(11) 4197 3600
Mexico	01800 5064 800
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 375 8100

Europe & Middle East

Belgium	32 (0) 2 404 93 40
Denmark	45 45 80 12 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
United Kingdom	44 (0) 118 927 6201

For other unlisted countries:

www.agilent.com/find/contactus

Revised: October 11, 2012

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2012
 Published in USA, October 16, 2012
 5989-8926EN



Agilent Technologies