

## Surface Mount Schottky Barrier Rectifier

### FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guardring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



### MECHANICAL DATA

**Case:** DO-214AB (SMC)

Molding compound, UL flammability classification rating 94V-0

Base P/N with suffix "G" on packing code - halogen-free

Base P/N with prefix "H" on packing code - AEC-Q101 qualified

**Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 1A whisker test

with prefix "H" on packing code meet JESD 201 class 2 whisker test

**Polarity:** Indicated by cathode band

**Weight:** 0.21 g (approximately)

DO-214AB (SMC)

| MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> =25°C unless otherwise noted)                   |                    |              |          |          |          |              |          |              |           |              |      |
|----------------------------------------------------------------------------------------------------------------|--------------------|--------------|----------|----------|----------|--------------|----------|--------------|-----------|--------------|------|
| PARAMETER                                                                                                      | SYMBOL             | SS<br>32     | SS<br>33 | SS<br>34 | SS<br>35 | SS<br>36     | SS<br>39 | SS<br>310    | SS<br>315 | SS<br>320    | Unit |
| Maximum repetitive peak reverse voltage                                                                        | V <sub>RRM</sub>   | 20           | 30       | 40       | 50       | 60           | 90       | 100          | 150       | 200          | V    |
| Maximum RMS voltage                                                                                            | V <sub>RMS</sub>   | 14           | 21       | 28       | 35       | 42           | 63       | 70           | 105       | 140          | V    |
| Maximum DC blocking voltage                                                                                    | V <sub>DC</sub>    | 20           | 30       | 40       | 50       | 60           | 90       | 100          | 150       | 200          | V    |
| Maximum average forward rectified current                                                                      | I <sub>F(AV)</sub> | 3            |          |          |          |              |          |              |           |              | A    |
| Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load                            | I <sub>FSM</sub>   | 100          |          |          |          | 70           |          |              |           |              | A    |
| Maximum instantaneous forward voltage (Note 1)<br>I <sub>F</sub> = 3 A @ 25°C<br>I <sub>F</sub> = 3 A @ 100°C  | V <sub>F</sub>     | 0.5<br>0.4   |          |          |          | 0.75<br>0.65 |          | 0.85<br>0.70 |           | 0.95<br>0.80 | V    |
| Maximum reverse current @ rated VR    T <sub>J</sub> =25 °C<br>T <sub>J</sub> =100°C<br>T <sub>J</sub> =125 °C | I <sub>R</sub>     | 0.5          |          |          |          |              | 0.1      |              |           |              | mA   |
|                                                                                                                |                    | 10           |          |          | 5        |              | -        |              |           |              |      |
|                                                                                                                |                    | -            |          |          | -        |              | 0.5      |              |           |              |      |
| Voltage rate of change (Rated V <sub>R</sub> )                                                                 | dV/dt              | 10000        |          |          |          |              |          |              |           |              | V/μs |
| Typical thermal resistance                                                                                     | R <sub>θJL</sub>   | 17           |          |          |          |              |          |              |           |              | °C/W |
|                                                                                                                | R <sub>θJA</sub>   | 55           |          |          |          |              |          |              |           |              |      |
| Operating junction temperature range                                                                           | T <sub>J</sub>     | - 55 to +125 |          |          |          | - 55 to +150 |          |              |           |              | °C   |
| Storage temperature range                                                                                      | T <sub>STG</sub>   | - 55 to +150 |          |          |          |              |          |              |           |              | °C   |

Note 1: Pulse test with PW=300μs, 1% duty cycle

| ORDERING INFORMATION |                    |              |                     |         |                          |
|----------------------|--------------------|--------------|---------------------|---------|--------------------------|
| PART NO.             | AEC-Q101 QUALIFIED | PACKING CODE | GREEN COMPOUND CODE | PACKAGE | PACKING                  |
| SS3xx<br>(Note 1)    | Prefix "H"         | R7           | Suffix "G"          | SMC     | 850 / 7" Plastic reel    |
|                      |                    | R6           |                     | SMC     | 3,000 / 13" Paper reel   |
|                      |                    | M6           |                     | SMC     | 3,000 / 13" Plastic reel |

Note 1: "xx" defines voltage from 20V (SS32) to 200V (SS320)

| EXAMPLE       |          |                    |              |                     |                    |
|---------------|----------|--------------------|--------------|---------------------|--------------------|
| PREFERRED P/N | PART NO. | AEC-Q101 QUALIFIED | PACKING CODE | GREEN COMPOUND CODE | DESCRIPTION        |
| SS36 R7       | SS36     |                    | R7           |                     |                    |
| SS36 R7G      | SS36     |                    | R7           | G                   | Green compound     |
| SS36HR7       | SS36     | H                  | R7           |                     | AEC-Q101 qualified |

RATINGS AND CHARACTERISTICS CURVES

(TA=25°C unless otherwise noted)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS




FIG. 5 TYPICAL JUNCTION CAPACITANCE






FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE




## PACKAGE OUTLINE DIMENSIONS



| DIM. | Unit (mm) |      | Unit (inch) |       |
|------|-----------|------|-------------|-------|
|      | Min       | Max  | Min         | Max   |
| A    | 2.90      | 3.20 | 0.114       | 0.126 |
| B    | 6.60      | 7.11 | 0.260       | 0.280 |
| C    | 5.59      | 6.22 | 0.220       | 0.245 |
| D    | 2.00      | 2.62 | 0.079       | 0.103 |
| E    | 1.00      | 1.60 | 0.039       | 0.063 |
| F    | 7.75      | 8.13 | 0.305       | 0.320 |
| G    | 0.10      | 0.20 | 0.004       | 0.008 |
| H    | 0.15      | 0.31 | 0.006       | 0.012 |

## SUGGESTED PAD LAYOUT



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 3.3       | 0.130       |
| B      | 2.5       | 0.098       |
| C      | 6.8       | 0.268       |
| D      | 4.4       | 0.173       |
| E      | 9.4       | 0.370       |

## MARKING DIAGRAM



P/N = Specific Device Code  
 G = Green Compound  
 YW = Date Code  
 F = Factory Code

### **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.