


IRF 620/FI-621/FI
IRF 622/FI-623/FI


S G S-THOMSON

N - CHANNEL ENHANCEMENT MODE
POWER MOS TRANSISTORS


TYPE	V _{DSS}	R _{DS(on)}	I _D *
IRF620	200 V	0.8 Ω	5 A
IRF620FI	200 V	0.8 Ω	4 A
IRF621	150 V	0.8 Ω	5 A
IRF621FI	150 V	0.8 Ω	4 A
IRF622	200 V	1.2 Ω	4 A
IRF622FI	200 V	1.2 Ω	3.5 A
IRF623	150 V	1.2 Ω	4 A
IRF623FI	150 V	1.2 Ω	3.5 A

- 200V FOR TELECOMMUNICATION APPLICATIONS
 - ULTRA FAST SWITCHING
 - RATED FOR UNCLAMPED INDUCTIVE SWITCHING (ENERGY TEST) ♦
 - EASY DRIVE - REDUCES COST AND SIZE
- INDUSTRIAL APPLICATIONS:**
- SWITCHING MODE POWER SUPPLIES
 - DC SWITCH
 - ROBOTCS


N - channel enhancement mode POWER MOS field effect transistors. Easy drive and very fast switching times make these POWER MOS transistors ideal for high speed switching applications. Typical uses are in telecommunications, robotics, switching power supplies and as a DC switch.



TO-220



ISOWATT220

INTERNAL SCHEMATIC DIAGRAM

ABSOLUTE MAXIMUM RATINGS

		TO-220		IRF				
		ISOWATT220		620	621	622	623	
V _{DS} *	Drain-source voltage (V _{GS} = 0)			200	150	200	150	V
V _{DGR} *	Drain-gate voltage (R _{GS} = 20 KΩ)			200	150	200	150	V
V _{GS}	Gate-source voltage					±20		V
I _{DM} (*)	Drain current (pulsed)			20	20	16	16	A
I _D	Drain current (cont.) at T _c = 25°C			5	5	4	4	A
I _D	Drain current (cont.) at T _c = 100°C			3	3	2.5	2.5	A
I _D ■	Drain current (cont.) at T _c = 25°C			620FI	621FI	622FI	623FI	A
I _D ■	Drain current (cont.) at T _c = 100°C			4	4	3.5	3.5	A
				2.5	2.5	2	2	A
P _{tot}	Total dissipation at T _c < 25°C			TO-220		ISOWATT220		W
	Derating factor			40		30		W/°C
T _{stg}	Storage temperature			0.32		0.24		W/°C
T _j	Max. operating junction temperature					-55 to 150		°C
						150		°C

* T_j = 25°C to 125°C

(•) Repetitive Rating: Pulse width limited by max junction temperature.

■ See note on ISOWATT220 on this datasheet.

♦ Introduced in 1988 week 44

30E D ■ 7929237 0029784 3 ■

T-39-11

THERMAL DATA

TO-220 ISOWATT220

$R_{thj} - case$	Thermal resistance junction-case	max	3.12	4.16	°C/W
R_{thc-s}	Thermal resistance case-sink	typ	0.5		°C/W
$R_{thj-amb}$	Thermal resistance junction-ambient	max	80		°C/W
T_l	Maximum lead temperature for soldering purpose		300		°C

ELECTRICAL CHARACTERISTICS ($T_{case} = 25^\circ\text{C}$ unless otherwise specified)

Parameters	Test Conditions	Min.	Typ.	Max.	Unit
------------	-----------------	------	------	------	------

OFF

$V_{(BR) DSS}$	Drain-source breakdown voltage	$I_D = 250 \mu\text{A}$ for IRF620/622/620FI/622FI for IRF621/623/621FI/623FI	$V_{GS} = 0$	200 150	V V
I_{DSS}	Zero gate voltage drain current ($V_{GS} = 0$)	$V_{DS} = \text{Max Rating}$ $V_{DS} = \text{Max Rating} \times 0.8$	$T_c = 125^\circ\text{C}$	250 1000	μA μA
I_{GSS}	Gate-body leakage current ($V_{DS} = 0$)	$V_{GS} = \pm 20 \text{ V}$		± 500	nA

ON **

$V_{GS(th)}$	Gate threshold voltage	$V_{DS} = V_{GS}$	$I_D = 250 \mu\text{A}$	2	4	V
$I_{D(on)}$	On-state drain current	$V_{DS} > I_{D(on)} \times R_{DS(on) max}$ for IRF620/621/620FI/621FI for IRF622/623/622FI/623FI	$V_{GS} = 10 \text{ V}$	5 4		A A
$R_{DS(on)}$	Static drain-source on resistance	$V_{GS} = 10 \text{ V}$ for IRF620/621/620FI/621FI for IRF622/623/622FI/623FI	$I_D = 2.5 \text{ A}$		0.8 1.2	Ω Ω

ENERGY TEST

I_{UIS}	Unclamped inductive switching current (single pulse)	$V_{DD} = 30 \text{ V}$ starting $T_l = 25^\circ\text{C}$ for IRF620/621/620FI/621FI for IRF622/623/622FI/623FI	$L = 100 \mu\text{H}$	5 4		A A
-----------	--	--	-----------------------	--------	--	--------

DYNAMIC

g_{fs}^{**}	Forward transconductance	$V_{DS} > I_{D(on)} \times R_{DS(on) max}$ $I_D = 2.5 \text{ A}$	1.3			mho
C_{iss}	Input capacitance	$V_{DS} = 25 \text{ V}$	$f = 1 \text{ MHz}$		600	pF
C_{oss}	Output capacitance	$V_{GS} = 0$			300	pF
C_{rss}	Reverse transfer capacitance				80	pF

30E D ■ 7929237 0029785 5 ■

ELECTRICAL CHARACTERISTICS (Continued)

T-39-11

Parameters	Test Conditions	Min.	Typ.	Max.	Unit
t_d (on) t_r t_d (off) t_f	Turn-on time Rise time Turn-off delay time Fall time $V_{DD} = 75\text{ V}$ $I_D = 2.5\text{ A}$ $R_l = 50\ \Omega$ (see test circuit)			40 60 100 60	ns ns ns ns
Q_g	Total Gate Charge $V_{GS} = 10\text{ V}$ $I_D = 6\text{ A}$ $V_{DS} = \text{Max Rating} \times 0.8$ (see test circuit)			15	nC

SWITCHING




SOURCE DRAIN DIODE

I_{SD} I_{SDM} (*)	Source-drain current Source-drain current (pulsed)			5 20	A A
V_{SD}^{**}	Forward on voltage	for IRF620/621/620FI/621FI $I_{SD} = 5\text{ A}$ $V_{GS} = 0$ for IRF622/623/622FI/623FI $I_{SD} = 4\text{ A}$ $V_{GS} = 0$		1.8 1.4	V V
t_{rr} Q_{rr}	Reverse recovery time Reverse recovered charge	$I_{SD} = 5\text{ A}$ $di/dt = 100\text{ A}/\mu\text{s}$	350 2.3		ns μC

** Pulsed: Pulse duration $\leq 300\ \mu\text{s}$, duty cycle $\leq 1.5\%$

(*) Repetitive Rating: Pulse width limited by max junction temperature

■ See note on ISOWATT220 In this datasheet

Safe operating areas
(standard package)Thermal impedance
(standard package)Derating curve
(standard package)




30E D ■ 7929237 0029786 7 ■

T-39-11

Output characteristics

Output characteristics




Transfer characteristics



Transconductance

Static drain-source on resistance




Maximum drain current vs temperature



Gate charge vs gate-source voltage



Capacitance variation

Normalized breakdown voltage vs temperature




30E D ■ 7929237 0029787 9 ■

T-39-11


Normalized on resistance
vs temperatureSource-drain diode forward
characteristics

Unclamped inductive test circuit




SC-0339

Unclamped inductive waveforms




SC-0338

Switching times test circuit



SC-0246

Gate charge test circuit



SC-0244

ISOWATT220 PACKAGE CHARACTERISTICS AND APPLICATION.

ISOWATT220 is fully isolated to 2000V dc. Its thermal impedance, given in the data sheet, is optimised to give efficient thermal conduction together with excellent electrical isolation.

The structure of the case ensures optimum distances between the pins and heatsink. The ISOWATT220 package eliminates the need for external isolation so reducing fixing hardware. Accurate moulding techniques used in manufacture assure consistent heat spreader-to-heatsink capacitance.

ISOWATT220 thermal performance is better than that of the standard part, mounted with a 0.1mm mica washer. The thermally conductive plastic has a higher breakdown rating and is less fragile than mica or plastic sheets. Power derating for ISOWATT220 packages is determined by:

$$P_D = \frac{T_J - T_C}{R_{th}}$$

from this I_{Dmax} for the POWER MOS can be calculated:

$$I_{Dmax} \leq \sqrt{\frac{P_D}{R_{DS(on)} \text{ (at } 150^\circ\text{C)}}}$$

THERMAL IMPEDANCE OF ISOWATT220 PACKAGE

Fig. 1 illustrates the elements contributing to the thermal resistance of transistor heatsink assembly, using ISOWATT220 package.

The total thermal resistance $R_{th \text{ (tot)}}$ is the sum of each of these elements.

The transient thermal impedance, Z_{th} for different pulse durations can be estimated as follows:

1 - for a short duration power pulse less than 1ms;

$$Z_{th} < R_{thJ-C}$$

2 - for an intermediate power pulse of 5ms to 50ms:


$$Z_{th} = R_{thJ-C}$$

3 - for long power pulses of the order of 500ms or greater:

$$Z_{th} = R_{thJ-C} + R_{thC-HS} + R_{thHS-amb}$$


It is often possible to discern these areas on transient thermal impedance curves.

Fig. 1




ISOWATT DATA

Safe operating areas



Thermal impedance



Derating curve

