

## AIH Series

250 Watts

**Total Power:** 250 Watts  
(12V @ 20.8A)  
**Input Voltage:** 300V  
**# of Outputs:** Single

### Special Features

- 250W Continuous power at 100°C baseplate temperature
- High efficiency - up to 88%
- Low output ripple and noise
- Positive and Negative enable function
- Excellent transient response
- Safety isolated low voltage control and monitoring
- High reliability
- Wide input voltage range
- Paralleable with accurate current sharing
- Adjustable output voltage
- Regulation to zero load
- Temperature monitor output
- EU Directive 2002/95/EC compliant for RoHS

### Safety

UL 60950 Recognized  
cUL 60950 Recognized  
TUV EN60950 Licensed  
CE CE Mark



Rev. 04.25.11  
AIH Series  
1 of 2



## Electrical Specifications

### Input

|             |                      |
|-------------|----------------------|
| Input range | 250 - 420 VDC        |
| Input surge | 450V / 100ms         |
| Efficiency* | 88% @ 5.0V (typical) |

### Output

|                             |                                                                                                          |
|-----------------------------|----------------------------------------------------------------------------------------------------------|
| Load Regulation             | 0.2% typical (5V and above); 10mV for below 5V                                                           |
| Line Regulation             | 0.2% typical (5V and above); 10mV for below 5V                                                           |
| Noise / ripple              | 100mV typical (below 5V); 2% typical (5V and above)                                                      |
| Output voltage adjust range | +/-20% for 5V and above; +10%/-50% for below 5V                                                          |
| Transient response          | 5% max for 3.3V and above 150mV for 1.8V, deviation with 25% to 75% full load 250 $\mu$ S (max) recovery |
| Current share accuracy      | 3% typical                                                                                               |
| Overvoltage protection      | 130% Vo (3.3 Vo and 5 Vo); 125% Vo (other Vo)                                                            |
| Current limit               | 120% Io maximum                                                                                          |

### Control

|                             |                                                       |
|-----------------------------|-------------------------------------------------------|
| Voltage adjust              | 80 to 120% for 5V and above; +10% / -50% for below 5V |
| Enable                      | TTL compatible (positive & negative enable options)   |
| Clock input (external sync) | 3.3 to 5.5Vp-p @800 MHz $\pm$ 5%                      |
| Temperature monitor output  | 10mV/°K (2.73 = 0°C)                                  |
| Current monitor output      | 0 to 1mA (1mA = 100% Io rated)                        |

### Notes

Nominal values apply with sense pins disconnected and other control pin unconnected.

\*For detailed technical information, please refer to the product's Technical Reference Notes found at [www.PowerConversion.com](http://www.PowerConversion.com).



## Environmental Specifications

|                            |                                    |
|----------------------------|------------------------------------|
| Operating temperature      | -20°C to +100°C (case temperature) |
| Startup temperature        | -40°C to +100°C (case temperature) |
| Storage temperature        | -40°C to +100°C                    |
| Overtemperature protection | 120°C max                          |
| MTBF                       | 1M hours (Demonstrated)            |

## Ordering Information


| Input Voltage | Output Voltage | Efficiency | Model Number |
|---------------|----------------|------------|--------------|
| 300V          | 1.8V @ 50A     | 80% (Typ)  | AIH50Y300    |
| 300V          | 3.3V @ 50A     | 82% (Typ)  | AIH50F300    |
| 300V          | 5.0V @ 40A     | 88% (Typ)  | AIH40A300    |
| 300V          | 12V @ 20.8A    | 86% (Typ)  | AIH20B300    |
| 300V          | 15V @ 16.6A    | 90% (Typ)  | AIH16C300    |
| 300V          | 24V @ 10.4A    | 90% (Typ)  | AIH10H300    |

1. For Negative enable add suffix "N".
2. For Non-thread hole, add suffix "-NT".
3. For RoHS 6, add suffix "-L". Default is RoHS 5.

## Pin Assignments

| Input        | Output       | Control Pins |
|--------------|--------------|--------------|
| 31. Positive | 22. Positive | 1. +Sense    |
| 32. Negative | 23. Positive | 2. Temp Mon  |
|              | 24. Positive | 3. C Mon     |
|              | 27. Negative | 4. C Share   |
|              | 28. Negative | 5. SDA       |
|              | 29. Negative | 6. SCL       |
|              |              | 7. CLK IN    |
|              |              | 8. V Adj     |
|              |              | 9. Enable    |
|              |              | 10. -Sense   |

## Mechanical Drawing



## Americas

5810 Van Allen Way  
Carlsbad, CA 92008  
USA  
Telephone: +1 760 930 4600  
Facsimile: +1 760 930 0698

## Europe (UK)

Waterfront Business Park  
Merry Hill, Dudley  
West Midlands, DY5 1LX  
United Kingdom  
Telephone: +44 (0) 1384 842 211  
Facsimile: +44 (0) 1384 843 355

## Asia (HK)

14/F, Lu Plaza  
2 Wing Yip Street  
Kwun Tong, Kowloon  
Hong Kong  
Telephone: +852 2176 3333  
Facsimile: +852 2176 3888

For global contact, visit:

[www.Emerson.com/EmbeddedPower](http://www.Emerson.com/EmbeddedPower)  
[techsupport.embeddedpower@emerson.com](mailto:techsupport.embeddedpower@emerson.com)

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

## Emerson Network Power.

The global leader in enabling business-critical continuity.

- AC Power
- Connectivity
- DC Power
- Embedded Computing
- Embedded Power
- Monitoring
- Outside Plant
- Power Switching & Controls
- Precision Cooling
- Racks & Integrated Cabinets
- Services
- Surge Protection

[EmersonNetworkPower.com](http://EmersonNetworkPower.com)

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.  
©2011 Emerson Electric Co.