


PRX+2452



PRX+2452

Ultraminiature SMD Reed
Switch

Electrical Characteristics

@ 25 °C

Contact form		A
Contact material		Durel
Contact rating max.	W / VA	0.25
Switching voltage max.	VDC	30
	VAC	30
Switching current max.	A	0.01
Carry current max.	A	0.1
Breakdown voltage min.	VDC	80
Contact resistance max. (initial)	mΩ	1
Insulation resistance min.	Ω	10 ¹¹

Magnetical Characteristics (of unmodified Reed Switch)

@ 25 °C

Pull in range available	AT	2 - 15
Drop out min.	AT	1
Test coil	TC	091
Test equipment tolerance	± AT	1

Operating Characteristics

@ 25 °C

Switching frequency max.	Hz	900
Resonant frequency typ.	Hz	10000
Operate time max. (incl. bounce)	ms	0.3
Release time max.	ms	0.2

Environmental Characteristics

Operating temperature	°C	-40 to +125
Storage temperature	°C	-40 to +200
Vibration (50-2000 Hz)	g	15
Shock (1/2 sin 11 ms)	g	75

Features


- Ultra miniature size
- Minimum height above PCB
- Suitable for lead-free soldering
- Suitable for automated assembly
- Tape & reel packaging upon request
- Not ESD sensitive
- Various sensitivity ranges available

Approvals

RoHS

REACH

Dimensions in mm



Ordering Information


Packing Unit	200 pcs
Weight per piece	0.02 g
Weight per package	16 g
Standard AT ranges	

2 to 4	AT
5 to 10	AT
10 to 15	AT

Ordering example

PRX+2452510 describes
PRX+2452 with 5 to 10 AT.


PRX+2452



PRX+2452

Ultraminiature SMD Reed
Switch

Recommended PCB Layout in mm



Pad sizes



Final assembly position

Remarks

When placed onto ferromagnetic parts
switching distance of PRX+2452
may reduce.

Electromagnetical influences and magnetic fields
may change the switching behaviour
of the SMD Reed Switch.