

STRUCTURE
TYPE
PRODUCT SERIES
FEATURES

Silicon Monolithic Integrated Circuit
Step down 2ch DC/DC converter Controller for Lap top PC
BD9535MUV
 • Built in 2ch H³REG DC/DC controller
 • Switching Frequency Variable (f=200kHz~600kHz)
 • Built in PGOOD function

○ ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

Parameter	Symbol	Limit	Unit
Input Voltage 1	VCC	7 *1	V
Input Voltage 2	VDD	7 *1	V
Input Voltage 3	VIN	30 *1	V
BOOT Voltage	VBOOT1/2	35 *1	V
BOOT-SW Voltage	VBOOT1-VSW1, VBOOT2-VSW2	7 *1	V
HG-SW Voltage	VHG1-VSW1, VHG2-VSW2	7 *1	V
LG Voltage	VLG1/2	VDD	V
Output Voltage Setting Voltage	VREF1/2	VCC	V
Output Voltage	V _{Is+1/2} , V _{Is-1/2}	VCC	V
SS Voltage	VSS1/2	VCC	V
FS Voltage	VFS	VCC	V
VREG Voltage	VREG	VCC	V
Current Limit Setting Voltage	VILIM1/2	VCC	V
Logic Input Voltage	VEN1/2	7 *1	V
PGOOD Voltage	VPGOOD1/2	7 *1	V
CE Voltage	VCE1/2	VREG	V
Power Dissipation 1	Pd1	0.38*2	W
Power Dissipation 2	Pd2	0.88*3	W
Power Dissipation 3	Pd3	2.06*4	W
Power Dissipation 4	Pd4	4.56*5	W
Operating Temperature Range	Topr	-10~+100	°C
Storage Temperature Range	Tstg	-55~+150	°C
Maximum Junction Temperature	Tjmax	+150	°C

*1 Not to exceed Pd, ASO, and Tjmax=150°C.

*2 Reduced by 3.0mW for each increase in Ta of 1°C over 25°C (when don't mounted on a heat radiation board)

*3 Reduced by 7.0mW for increase in Ta of 1°C over 25°C. (when mounted on a board 70.0mm × 70mm × 1.6mm Glass-epoxy PCB which has 1 layer. (Copper foil area : 0mm²))

*4 Reduced by 16.5mW for increase in Ta of 1°C over 25°C. (when mounted on a board 70.0mm × 70mm × 1.6mm Glass-epoxy PCB which has 4 layers. (1st and 4th copper foil area : 20.2mm², 2nd and 3rd copper foil area : 5505mm²))

*5 Reduced by 36.5mW for increase in Ta of 1°C over 25°C. (when mounted on a board 70.0mm × 70mm × 1.6mm Glass-epoxy PCB which has 4 layers. (All copper foil area : 5505mm²))

○ OPERATING CONDITIONS (Ta=25°C)

Parameter	Symbol	MIN	MAX	Unit
Input Voltage 1	VCC	4.5	5.5	V
Input Voltage 2	VDD	4.5	5.5	V
Input Voltage 3	VIN	3.0	28	V
BOOT Voltage	VBOOT1/2	4.5	33	V
SW Voltage	VSW1/2	-0.7	28	V
BOOT-SW Voltage	VHG1-VSW1, VHG2-VSW2	4.5	5.5	V
Logic Input Voltage	VEN1/2	0	5.5	V
Output setting voltage	VREF1/2	0.7	2.0	V
Is Input Voltage	V _{Is+1/2} , V _{Is-1/2}	0.7	2.0	V
Minimum ON Time	tomin	-	100	nsec

★ This product is not designed for protection against radioactive rays.

Status of this document

The Japanese version of this document is the official specification.


This translated version is intended only as a reference, to aid in understanding the official version.

If there are any differences between the original and translated versions of this document, the official Japanese language version takes priority.

○ELECTRICAL CHARACTERISTICS (unless otherwise noted, $T_a=25^\circ C$ $V_{CC}=5V, V_{DD}=5V, V_{EN1/2}=3V, V_{IN}=12V, V_{REF1/2}=1.8V, R_{FS}=68k\Omega$)

Parameter	Symbol	Standard Value			Unit	Condition
		MIN	TYP	MAX		
[Whole Device block]						
VCC Bias Current	I _{CC}	-	1.4	2.0	mA	
VIN Bias Current	I _{IN}	-	200	400	μA	
VCC Standby Current	I _{STB}	-	0	20	μA	$V_{EN1}=V_{EN2}=0V$
VIN Standby Current	I _{IN_STB}	-	0	40	μA	$V_{EN1}=V_{EN2}=0V$
EN Low Voltage1,2	V _{EN_low1,2}	GND	-	0.8	V	
EN High Voltage1,2 (Forced continuous mode)	V _{ENH_low1,2}	2.3	-	3.8	V	
EN High Voltage1,2(SLLM TM)	V _{ENH_sllm1,2}	4.2	-	5.5	V	
EN Bias Current1,2	I _{EN1,2}	-	7	10	μA	
VREG Voltage	V _{REG}	2.480	2.500	2.520	V	$I_{REG}=500\mu A$ $T_a=-10\sim 100^\circ C$
[Under Voltage Locked Out block]						
VCC threshold voltage	V _{CC_UVLO}	4.1	4.3	4.5	V	V _{CC} :Sweep up
VCC hysteresis voltage	dV _{CC_UVLO}	100	160	220	mV	V _{CC} :Sweep down
VIN threshold voltage	V _{IN_UVLO}	2.4	2.6	2.8	V	V _{IN} :Sweep up
VIN hysteresis voltage	dV _{IN_UVLO}	100	160	220	mV	V _{IN} :Sweep down
VREG threshold voltage	V _{REG_UVLO}	2.0	2.2	2.4	V	V _{REG} :Sweep up
VREG hysteresis voltage	dV _{REG_UVLO}	100	160	220	mV	V _{REG} :Sweep down
[Over Voltage Protection block]						
VOUT Threshold Voltage 1,2	V _{OUT_OVP1,2}	$V_{REF} \times 1.15$	$V_{REF} \times 1.20$	$V_{REF} \times 1.25$	V	
[Power Good block]						
VOUT POWER GOOD LOW Voltage1,2	V _{PGOOD_low1,2}	$V_{REF} \times 0.87$	$V_{REF} \times 0.90$	$V_{REF} \times 0.93$	V	
VOUT POWER GOOD HIGH Voltage1,2	V _{PGOOD_high1,2}	$V_{REF} \times 1.07$	$V_{REF} \times 1.10$	$V_{REF} \times 1.13$	V	
Discharge ON Resistance1,2	R _{ON_PGOOD1,2}	-	1.0	2.0	kΩ	
Delay Time1,2	t _{PGOOD1,2}	150	250	350	μsec	
[H³REGTM block]						
ON Time1	t _{on1}	400	500	600	nsec	R _{FS} =68kΩ
MAX ON Time1	t _{onmax1}	1.8	2.8	3.8	μsec	
MIN OFF Time1	t _{offmin1}	500	600	700	nsec	
ON Time2	t _{on2}	250	350	450	nsec	R _{FS} =68kΩ
MAX ON Time2	t _{onmax2}	1.0	1.8	2.6	μsec	
MIN OFF Time2	t _{offmin2}	500	600	700	nsec	
[FET Driver block]						
HG upper side ON Resistance1,2	R _{HGon1,2}	-	3.0	6.0	Ω	
HG Lower side ON Resistance 1,2	R _{HGlon1,2}	-	2.0	4.0	Ω	
LG upper side ON Resistance 1,2	R _{LGon1,2}	-	2.0	4.0	Ω	
LG Lower side ON Resistance 1,2	R _{LGlon1,2}	-	0.5	1.0	Ω	
[Soft start block]						
Charge Current 1,2	I _{SS1,2}	1.5	2	2.5	μA	
Discharge Current 1,2	I _{SS_dis1,2}	1.5	2	2.5	μA	
Discharge Threshold Voltage 1,2	V _{SS_dsth1,2}	-	0.1	0.2	V	
Standby Voltage 1,2	V _{SS_STB1,2}	-	-	50	mV	
[Current Limit block]						
Current Limit Threshold Voltage1_1,2	V _{ILIM1,2}	40	50	60	mV	V _{ILIM1,2} =0.5V
Current Limit Threshold Voltage2_1,2	V _{ILIM2,2}	170	200	230	mV	V _{ILIM1,2} =2.0V
[Output Voltage Sense block]						
V _{IS} offset voltage1,2	V _{IS_off1,2}	1.790	1.800	1.810	V	$T_a=-10\sim 100^\circ C$
REF bias current1,2	I _{REF1,2}	-150	0	150	nA	
I _{S+} input current1,2	I _{S+1,2}	-1.0	0	1.0	μA	V _{IS+1,2} =1.8V
I _{S-} input current1,2	I _{S-1,2}	-1.0	0	1.0	μA	V _{IS-1,2} =1.8V
[SCP block]						
Threshold Voltage1,2	V _{THSCP1,2}	$V_{REF} \times 0.65$	$V_{REF} \times 0.7$	$V_{REF} \times 0.75$	V	
Delay Time 1,2	t _{SCP1,2}	0.5	1	1.5	msec	


OPHYSICAL DIMENSIONS



(UNIT:mm)

VQFN032-V5050

OBLOCK DIAGRAM



OPIN No., PIN Name

PIN No.	PIN name
1	BOOT1
2	CE1
3	PGOOD1
4	EN1
5	SS1
6	ILIM1
7	REF1
8	VREG
9	FS
10	Is-1
11	Is+1
12	GND
13	VCC
14	Is+2
15	Is-2
16	VIN
17	REF2
18	ILIM2
19	SS2
20	EN2
21	PGOOD2
22	CE2
23	BOOT2
24	HG2
25	SW2
26	PGND2
27	LG2
28	VDD
29	LG1
30	PGND1
31	SW1
32	HG1
Bottom	FIN

REV. A

NOTES FOR USE

1. Absolute maximum ratings

An excess in the absolute maximum ratings, such as supply voltage, temperature range of operating conditions, etc., can break down the devices, thus making impossible to identify breaking mode, such as a short circuit or an open circuit. If any over rated values will expect to exceed the absolute maximum ratings, consider adding circuit protection devices, such as fuses.

2. GND voltage

The potential of GND, PGND1, PGND2 pin must be minimum potential in all operating conditions.

3. Thermal design

Use a thermal design that allows for a sufficient margin in light of the power dissipation (P_d) in actual operating conditions.

4. Inter-pin shorts and mounting errors

Use caution when positioning the IC for mounting on printed circuit boards. The IC may be damaged if there is any connection error or if pins are shorted together.

5. Actions in strong electromagnetic field

Use caution when using the IC in the presence of a strong electromagnetic field as doing so may cause the IC to malfunction.

6. ASO

When using the IC, set the output transistor so that it does not exceed absolute maximum ratings or ASO.

7. Testing on application boards

When testing the IC on an application board, connecting a capacitor to a pin with low impedance subjects the IC to stress. Always discharge capacitors after each process or step. Always turn the IC's power supply off before connecting it to or removing it from a jig or fixture during the inspection process. Ground the IC during assembly steps as an antistatic measure. Use similar precaution when transporting or storing the IC.


8. Electrical characteristics

The electrical characteristics in the Specifications may vary depending on ambient temperature, power supply voltage, circuit(s) externally applied, and/or other conditions. It is therefore requested to carefully check them including transient characteristics.

9. Not of a radiation-resistant design.

10. In the event that load containing a large inductance component

is connected to the output terminal, and generation of back-EMF at the start-up and when output is turned OFF is assumed, it is requested to insert a protection diode.



11. Regarding input pin of the IC


This monolithic IC contains P+ isolation and P substrate layers between adjacent elements in order to keep them isolated.

P-N junctions are formed at the intersection of these P layers with the N layers of other elements, creating a parasitic diode or transistor. For example, the relation between each potential is as follows:

When GND > Pin A and GND > Pin B, the P-N junction operates as a parasitic diode.

When GND > Pin B, the P-N junction operates as a parasitic transistor.

Parasitic diodes can occur inevitable in the structure of the IC. The operation of parasitic diodes can result in mutual interference among circuits, operational faults, or physical damage. Accordingly, methods by which parasitic diodes operate, such as applying a voltage that is lower than the GND (P substrate) voltage to an input pin, should not be used.



12. Ground Wiring Pattern

When using both small signal and large current GND patterns, it is recommended to isolate the two ground patterns, placing a single ground point at the ground potential of application so that the pattern wiring resistance and voltage variations caused by large currents do not cause variations in the small signal ground voltage. Be careful not to change the GND wiring pattern of any external components, either.

13. Operating ranges

If it is within the operating ranges, certain circuit functions and operations are warranted in the working ambient temperature range. With respect to characteristic values, it is unable to warrant standard values of electric characteristics but there are no sudden variations in characteristic values within these ranges.

14. Thermal shutdown circuit

This IC is provided with a built-in thermal shutdown (TSD) circuit, which is activated when the chip temperature reaches the threshold value listed below. When TSD is on, the device goes to high impedance mode. Note that the TSD circuit is provided for the exclusive purpose shutting down the IC in the presence of extreme heat, and is not designed to protect the IC per se or guarantee performance when or after extreme heat conditions occur. Therefore, do not operate the IC with the expectation of continued use or subsequent operation once the TSD is activated.

TSD ON temperature [°C] (typ.)	Hysteresis temperature [°C] (typ.)
175	15

15. Heat sink (FIN)

Since the heat sink (FIN) is connected with the Sub, short it to the GND.

Appendix

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.

Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available,
please contact your nearest sales office.

Please contact our sales offices for details ;

U.S.A / San Diego	TEL : +1(858)625-3630	FAX : +1(858)625-3670
Atlanta	TEL : +1(770)754-5972	FAX : +1(770)754-0691
Dallas	TEL : +1(972)312-8818	FAX : +1(972)312-0330
Germany / Dusseldorf	TEL : +49(2154)9210	FAX : +49(2154)921400
United Kingdom / London	TEL : +44(1)908-282-666	FAX : +44(1)908-282-528
France / Paris	TEL : +33(0)1 56 97 30 60	FAX : +33(0) 1 56 97 30 80
China / Hong Kong	TEL : +852(2)740-6262	FAX : +852(2)375-8971
Shanghai	TEL : +86(21)6279-2727	FAX : +86(21)6247-2066
Dilian	TEL : +86(411)8230-8549	FAX : +86(411)8230-8537
Beijing	TEL : +86(10)8525-2483	FAX : +86(10)8525-2489
Taiwan / Taipei	TEL : +866(2)2500-6956	FAX : +866(2)2503-2869
Korea / Seoul	TEL : +82(2)8182-700	FAX : +82(2)8182-715
Singapore	TEL : +65-6332-2322	FAX : +65-6332-5662
Malaysia / Kuala Lumpur	TEL : +60(3)7958-8355	FAX : +60(3)7958-8377
Philippines / Manila	TEL : +63(2)807-6872	FAX : +63(2)809-1422
Thailand / Bangkok	TEL : +66(2)254-4890	FAX : +66(2)256-6334

Japan /
(Internal Sales)

Tokyo	2-1-1, Yaesu, Chuo-ku, Tokyo 104-0082 TEL : +81(3)5203-0321	FAX : +81(3)5203-0300
Yokohama	2-4-8, Shin Yokohama, Kohoku-ku, Yokohama, Kanagawa 222-8575 TEL : +81(45)476-2131	FAX : +81(45)476-2128
Nagoya	Dainagayo Building 9F 3-28-12, Meieki, Nakamura-ku, Nagoya, Aichi 450-0002 TEL : +81(52)581-8521	FAX : +81(52)561-2173
Kyoto	579-32 Higashi Shiokouji-cho, Karasuma Nishi-iru, Shiokujidori, Shimogyo-ku, Kyoto 600-8216 TEL : +81(75)311-2121	FAX : +81(75)314-6559

(Contact address for overseas customers in Japan)

Yokohama	TEL : +81(45)476-9270	FAX : +81(045)476-9271
----------	-----------------------	------------------------