




■ Characteristic

Easy to grip by its longer neck.

■ Application

Distribution boards /
Distribution panels /
Control boards






The figure shows THA-207-1

Model No.	Key No.	Net Weight(g)	Code No.
THA-207-1	No.500	144	3652
THA-207-2	Without Key	138	3653

■Parts List

No.	Part Name	Material	Finish	Quantity
1	Handle	ZDC	Cr	1
2	Sleeve			1
3	Ring Washer	SUS304	—	1
4	Set Nut	ZDC	Zn	1
5	Square Hole Washer	SPCC		1
6	Cross Hole Head Hexagon Bolt with Washer	S		1
7	Lock	SUS304/ZDC	—/Zn	1
8	Key	BSP	Ni	2



For left turn
(Model No.2 only)

For right turn
(Both model No.1 and No.2)

Layout of Holes for Installation




■ Characteristic



The handle can be used for both left and right side by turning the flange.

■ Application

Small doors / Control boards, etc.



The figure shows the handle for right turn. Also the figure shows THA-199-1. The shape of THA-199-2 and THA-199-3 is slightly different.



For left turn For right turn

Layout of Holes for Installation

Model No.	Net Weight(g)	Code No.
THA-199-1	74	3589
THA-199-2	62	3592
THA-199-3	42	3594

■ Parts List

No.	Part Name	Material	Finish	Quantity
1	Handle	ZDC	Cr	1
2	Flange			1
3	Cross Hole Head Hexagon Bolt with Washer	S	Zn	1
4	Square Hole Washer	SPCC		1
5	Set Nut	ZDC		1
6	Ring Washer	SUS304	———	1
7	Flat Washer	SPCC	Zn	1

■ Size List

Model No.	A	B	C	D	E	F	G	H	J	K	N
THA-199-1	39	ϕ 8	31	(18)	7	9	2.5	ϕ 34	ϕ 2	13	ϕ 2.2
THA-199-2	32	ϕ 7	29	(16)		7	2	ϕ 33		15	
THA-199-3	28	ϕ 5	22		5			ϕ 23	ϕ 2.5	10.5	ϕ 2.2