




AK28089 SERIES



External Dimensions



Frame:Aluminum Alloy
Impeller:Plastic(UL:94V-0)
Motor Structure:Capacitor-Run Induction Motor.
Motor Protection:Thermal Protect.
Bearing:Ball bearing
Lead wire:UL1332AWG18
OPERATING TEMP*:-10°C~70°C
*:-10°C~60°C for fans with sleeve/ball combination bearings.



Specifications(Nominal)

*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Volt. (VAC)	Freq. (Hz)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow	Maximum		*Noise Level (dB/A)	Weight (g)	
									Pressure (InAq)	Pressure (mmAq)			
280x89	AK2881HB	◎	115	50/60	1.80/2.60	180.00/260.00	2800/3200	33.960/39.620	1200.0/1400.0	1.260/1.110	32.00/28.20	75.0/78.0	4240
	AK2882HB		230		0.78/1.22	177.10/260.00							

Specifications subject to change without notice.



*Safety approvals

				
✓	✓			