








MINIMUM HEIGHT OF SOCKET WITH
MODULE CARD HEIGHT OF 30.00MM
AND THICKNESS OF 4MM.

- NOTES :
- MATERIAL :
HOUSING : HIGH TEMPERATURE LIQUID CRYSTAL POLYMER, UL94V-0
COLOUR : BLACK
CONTACTS : COPPER ALLOY
LATCHES : HIGH TEMPERATURE NYLON, UL94V-0
COLOUR : NATURAL (OFF-WHITE)
COVER : HIGH TEMPERATURE NYLON, UL 94V-0
COLOUR : BLACK
 - FINISH
CONTACTS : 0.76 MICROMETER (30 MICROINCH) MIN GOLD OVER
1.25 MICROMETER (50 MICROINCH) MIN NICKEL
SMT TAIL : 2.54 MICROMETER (100 MICROINCH) MIN TIN OVER
1.25 MICROMETER (50 MICROINCH) MIN NICKEL
 - ACCEPTS 1.0mm THICK MEMORY MODULE PER JEDEC MO-244 FOR
244 CKTS AND MO-258 FOR 200 CKTS.
 - PRODUCT SPECIFICATION : PS-78035-001.
 - PACKING SPECIFICATION: SEE TABLE IN SHEET 4.


- △6 DATE CODE SHALL BE MARKED LEGIBLY AS
SHOWN : YY DDD.
- △7 PART NUMBER SHALL BE MARKED LEGIBLY
AS SHOWN : 78035-XXXX (REFER TO TABLE).

IMPROVE HOUSING EC NO: S2014-0671 DRW:KSOH 2013/03/11 CHKD:CGTAN 2014/02/10 APPR:SHLENI 2014/02/10	QUALITY SYMBOLS F _A =0 F _C =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY YTYANG01	DATE 2005/08/12	TITLE MINI DIMM, 0.60MM PITCH 200/244 CKTS, REV. ANGLE 22.5 DEG, SMT			
		4 PLACES	± ---	± ---	CHECKED BY SHLENI	DATE 2005/08/25				
		3 PLACES	± ---	± ---	APPROVED BY GGLEE	DATE 2005/08/25				
	2 PLACES	± 0.13	± ---	MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-78035-001	SHEET NO. 1 OF 4			
	1 PLACE	± 0.25	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
	0 PLACE	±	±	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						




IMPROVE HOUSING EC NO: S2014-0671 DRW: KEKSOH CHKD: CGTAN APPR: SHLENI 2013/03/11 2014/02/10 2014/02/10	QUALITY SYMBOLS $F_A = 0$ $F_B = 0$ $F_C = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		4 PLACES ± --- ± ---	mm INCH	DRAWN BY YTYANG01	DATE 2005/08/12	TITLE MINI DIMM, 0.60MM PITCH 200/244 CKTS, REV. ANGLE 22.5 DEG, SMT			
		3 PLACES ± --- ± ---		CHECKED BY SHLENI	DATE 2005/08/25	molex			
		2 PLACES ± 0.13 ± ---		APPROVED BY GGLEE	DATE 2005/08/25	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-78035-001	SHEET NO. 2 OF 4	
1 PLACE ± 0.25 ± ---		ANGULAR ± 1 °		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
0 PLACE ± ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							

10 9 8 7 6 5 4 3 2 1



RECOMMENDED PCB LAYOUT




Detail 4

IMPROVE HOUSING EC NO: S2014-0671 DRW: KEK30H CHKD: CGTAN APPR: SILENI 2013/03/11 2014/02/10 2014/02/10	DESCRIPTION REV G1	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
		$F_{\Delta} = 0$ $F_{\sigma} = 0$ $F_{\rho} = 0$	mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.13 ± --- 1 PLACE ± 0.25 ± --- 0 PLACE ± ±	MM ONLY	NTS	METRIC		
			ANGULAR ± 1 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DRAWN BY: YTYANG01 CHECKED BY: SHLENI APPROVED BY: GGLEE	DATE: 2005/08/12 DATE: 2005/08/25 DATE: 2005/08/25	TITLE: MINI DIMM, 0.60MM PITCH 200/244 CKTS, REV. ANGLE 22.5 DEG, SMT		
			SEE TABLE	MATERIAL NO. DOCUMENT NO.	molex SD-78035-001			

9 8 7 6 5 4 3 2 1

10 9 8 7 6 5 4 3 2 1



CKT. SIZE 'N'	PART NUMBER	MODULE CARD	VOLTAGE KEY	DIM 'R'	DIM 'E'	DIM 'J'	DIM 'L'	DIM 'M'	DIM 'P'	DIM 'G'	DIM 'S'	DIM 'T'	DIM 'U'	DIM 'V'	DIM 'W'	DIM 'X'	DIM 'Y'	DIM 'Z'	DIM 'A'	DIM 'B'	TRAY P/N PACKAGING SPEC
244	78035-0001	DDR2	1.8 V	1.30	39.60	38.40	33.60	37.0	79.0	89.80	96.0	106.20	78.00	82.00	78.0	82.00	96.20	42.50	93.0	75.60	89990-8198
	78035-0301	DDR3	1.5 V	2.30																	89990-8199
	78035-6301																				78888-8026
	78035-6001	DDR2	1.8 V	1.30																	PK-78035-003 (HARDTRAY)
200	78035-0201	DDR2	1.8 V	1.30	24.60	23.40	35.40	30.40	65.8	76.60	82.8	93.00	64.80	68.80	64.8	68.80	83.00	44.30	79.8	62.40	89990-8196
	78035-0202	DDR	2.5 V	2.30																	89990-8197
																					PK-78035-002

IMPROVE HOUSING EC NO: S2014-0671 DRW: NKS0H 2013/03/11 CHKD: CGTAN 2014/02/10 APPR: SHLENI 2014/02/10	QUALITY SYMBOLS $F_A=0$ $F_G=0$ $F_P=0$	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.13 ± --- 1 PLACE ± 0.25 ± --- 0 PLACE ± ± ANGULAR ± 1 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY DATE YTYANG01 2005/08/12 CHECKED BY DATE SHLENI 2005/08/25 APPROVED BY DATE GGLEE 2005/08/25	SCALE NTS DESIGN UNITS METRIC THIRD ANGLE PROJECTION	TITLE MINI DIMM, 0.60MM PITCH 200/244 CKTS, REV. ANGLE 22.5 DEG, SMT molex	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-78035-001	SHEET NO. 4 OF 4
	REV G1			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

9 8 7 6 5 4 3 2 1