

**Part Number: 91813-9113**

5.08 Pitch, KK®, CRP Terminal HSG, Glow Wire compatible, 13 Circuits, White, with Ramp, Glow Wire Compatible



Series image - Reference only

<b>Status:</b>	<b>OBSOLETE</b>
<b>Replacement:</b>	Contact Molex
<b>Series:</b>	<a href="#">91813</a>
<b>Category:</b>	Crimp Housings
<b>Overview:</b>	<a href="#">KK® Interconnection System</a>

**Mates With Part(s):**KK® Header [3003](#), [2599](#)**Use With:**KK® Crimp Terminal [2478](#), [2578](#)**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:****REACH SVHC:** Contains SVHC: No**Low-Halogen Status:** Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	Crimp Housings
Series	<a href="#">91813</a>
Application	Power
Comments	<p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies :</p> <p>a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.</p> <p>b) A Glow Wire Flammability Index (GWF1) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.</p> <p>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).</p> <p>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.</p>
Overview	<a href="#">KK® Interconnection System</a>
Product Name	KK®

**Physical**

Breakaway	No
Circuits (maximum)	13
Color - Resin	Natural (White)
Gender	Female
Glow-Wire Compliant	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	0°C to +75°C

**Material Info**

UPC	800756784885
-----	--------------

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application  
Tooling**

[Check our list of old tooling that used to be  
available for this part](#)