




TERMINALS STAMPED WITH THE LETTER "B"
ACCEPT 32-36 AWG WIRE WITH A 0.64 MAX INSULATION DIA

- NOTES:
- MATERIAL: PHOSPHOR BRONZE
 - PLATING:
124 = OVERALL BRIGHT TIN: 3.75 MICROMETERS MIN OVER NICKEL
207 = SELECT HARD GOLD: 0.38 MICROMETERS MIN.
SELECT TIN: 2.0 MICROMETERS MIN BOTH OVER NICKEL
206 = SELECT HARD GOLD: 0.75 MICROMETERS MIN.
SELECT TIN: 2.0 MICROMETERS MIN BOTH OVER NICKEL
216 = SELECT HARD GOLD: 1.27 MICROMETERS MIN.
SELECT TIN: 2.54 MICROMETERS MIN BOTH OVER NICKEL
P124 = PREPLATED OVERALL BRIGHT TIN: 3.75 MICROMETERS MIN OVER NICKEL
(MAY HAVE UNPLATED EDGES)
 - PRODUCT SPECIFICATION: TERMINALS CONFORM TO PS-70058 AND PS-70400 WHEN CRIMPED WITH MOLEX CRIMP TOOLS.
 - COSMETIC SPECIFICATION: PS-45499-002 CLASS B
 - TERMINAL FOR USE WITH HOUSING SERIES 70066 AND 70450
 - WIRE SPECIFICATION: TERMINALS STAMPED WITH THE LETTER:
A = ACCEPTS 24-30 AWG STRANDED WIRE WITH A 1.52 MAX INSULATION DIA
B = ACCEPTS 32-36 AWG STRANDED WIRE WITH A 0.64 MAX INSULATION DIA.
C = ACCEPTS 22-24 AWG STRANDED WIRE WITH A 1.63 MAX INSULATION DIA

CURRENT PART NUMBER	REPLACEMENT PART NUMBER	PACKAGING	PLATING SEE NOTE 2	WIRE SIZE	MAX INSULATION DIA
16-02-0084	70058-1084	REEL	124 OVERALL TIN	32 - 36 AWG	0.64 DIA MAX
16-02-0099	70058-1099	LOOSE			
70058-4084	70058-0084	REEL	P124 OVERALL TIN		
70058-4099	70058-0099	LOOSE			
16-02-0074	70058-0074	REEL	207 0.38 GOLD		
16-02-0100	70058-0100	LOOSE			
16-02-0085	70058-0085	REEL	206 0.75 GOLD		
16-02-0101	70058-0101	LOOSE			
16-02-0143	70058-0143	REEL	216 1.27 GOLD		
16-02-0144	70058-0144	LOOSE			

TERMINALS ON THIS SHEET ARE FOR USE
WITH 32-36 AWG WIRE.
SEE SHEETS 1 AND 3 FOR OTHER WIRE SIZES

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>	NONE	EC NO: 119821 DRWN: KSAMIEC CHK'D: APPR: FSMITH	2017/07/25	2017/07/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		<div><div>molex®</div><div>SL CRIMP TERMINAL (32-36 AWG WIRE)</div></div>													
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>							MM		8:1															
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					ANGULAR TOL ± °		DRWN BY				DATE				<div>PRODUCT CUSTOMER DRAWING</div>									
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>							KSAMIEC				2017/05/03													
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					4 PLACES		±		CHK'D BY				DATE				<div></div>							
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					3 PLACES		±		CHKD BY															
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					2 PLACES		± 0.25		APPR BY				DATE											
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					1 PLACE		± 0.15		FSMITH				2017/06/16											
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					0 PLACES		± 0.0		DRAWING SIZE				THIRD ANGLE PROJECTION				SERIES		MATERIAL NUMBER			CUSTOMER		
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		B		<div><div><div></div></div><div><div></div></div></div>				70058		<div></div>			<div></div>						
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>																								
<div><div><div><div></div></div><div></div></div><div>= 0</div></div>	A1		REV														DOCUMENT NUMBER			DOC TYPE		DOC PART		SHEET NUMBER
											700580000-SD			PSD		000		2 OF 4						



TERMINALS STAMPED WITH THE LETTER "C"
ACCEPT 22-24 AWG WIRE WITH A 1.63 MAX INSULATION DIA


- NOTES:
1. MATERIAL: PHOSPHOR BRONZE
 2. PLATING:
124 = OVERALL BRIGHT TIN: 3.75 MICROMETERS MIN OVER NICKEL
207 = SELECT HARD GOLD: 0.38 MICROMETERS MIN.
SELECT TIN: 2.0 MICROMETERS MIN BOTH OVER NICKEL
206 = SELECT HARD GOLD: 0.75 MICROMETERS MIN.
SELECT TIN: 2.0 MICROMETERS MIN BOTH OVER NICKEL
216 = SELECT HARD GOLD: 1.27 MICROMETERS MIN.
SELECT TIN: 2.54 MICROMETERS MIN BOTH OVER NICKEL
P124 = PREPLATED OVERALL BRIGHT TIN: 3.75 MICROMETERS MIN OVER NICKEL
(MAY HAVE UNPLATED EDGES)
 3. PRODUCT SPECIFICATION: TERMINALS CONFORM TO PS-70058 AND PS-70400 WHEN CRIMPED WITH MOLEX CRIMP TOOLS.
 4. COSMETIC SPECIFICATION: PS-45499-002 CLASS B
 5. TERMINAL FOR USE WITH HOUSING SERIES 70066 AND 70450
 6. WIRE SPECIFICATION: TERMINALS STAMPED WITH THE LETTER:
A = ACCEPTS 24-30 AWG STRANDED WIRE WITH A 1.52 MAX INSULATION DIA
B = ACCEPTS 32-36 AWG STRANDED WIRE WITH A 0.64 MAX INSULATION DIA.
C = ACCEPTS 22-24 AWG STRANDED WIRE WITH A 1.63 MAX INSULATION DIA

CURRENT PART NUMBER	REPLACEMENT PART NUMBER	PACKAGING	PLATING SEE NOTE 2	WIRE SIZE	MAX INSULATION DIA
16-02-0086	70058-1086	REEL	124 OVERALL TIN	22-24 AWG	1.63 DIA MAX
16-02-0102	70058-1102	LOOSE			
70058-4086	70058-0086	REEL	P124 OVERALL TIN		
70058-4102	70058-0102	LOOSE			
16-02-0087	70058-0087	REEL	207 0.38 GOLD		
16-02-0103	70058-0103	LOOSE			
16-02-0088	70058-0088	REEL	206 0.75 GOLD		
16-02-0104	70058-0104	LOOSE			
16-02-0131	70058-0131	REEL	216 1.27 GOLD		
16-02-0147	70058-0147	LOOSE			

TERMINALS ON THIS SHEET ARE FOR USE
WITH 22-24 AWG WIRE.
SEE SHEETS 1 AND 2 FOR OTHER WIRE SIZES


QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						
<div><div>F</div><div>A</div></div> = 0	NONE	EC NO: 119821	2017/07/25	DRWN: KSAMIEC	CHK'D:	2017/07/26	FSMITH	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE		<div><div>molex®</div><div>SL CRIMP TERMINAL (22-24 AWG WIRE)</div></div>										
<div><div>E</div><div>C</div></div> = 0									MM		8:1												
<div><div>F</div><div>C</div></div> = 0									DRWN BY		DATE		PRODUCT CUSTOMER DRAWING										
<div><div>F</div><div>P</div></div> = 0									KSAMIEC		2017/05/03												
<div><div>F</div><div>P</div></div> = 0									CHK'D BY		DATE		SERIES					MATERIAL NUMBER		CUSTOMER			
<div><div>F</div><div>P</div></div> = 0									CHKD BY														
<div><div>F</div><div>P</div></div> = 0									APPR BY		DATE		70058										
<div><div>F</div><div>P</div></div> = 0									FSMITH		2017/06/16												
<div><div>F</div><div>P</div></div> = 0									DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER					DOC TYPE		DOC PART		SHEET NUMBER	
<div><div>F</div><div>P</div></div> = 0									B		<div><div><div></div><div></div></div><div><div></div><div></div></div></div>												
<div><div>F</div><div>P</div></div> = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		<div><div>700580000-SD</div><div>PSD</div><div>000</div><div>3 OF 4</div></div>																				

REEL PACKED



UNWINDING DIRECT
TO CRIMP MACHINE


PARTS PER REEL: 20,000
REELS PER BOX: 3
PARTS PER BOX: 60,000




LOOSE PACKED



PARTS PER BAG: 10,000
BAGS PER BOX: 2
PARTS PER BOX: 20,000



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
QUALITY SYMBOLS		NONE EC NO: 119821 DRWN: KSAMIEC CHK'D: APPR: FSMITH		2017/07/25 2017/07/26		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		<div>molex®</div> <div>SL CRIMP TERMINAL</div>							
<div><div>F</div>A = 0</div> <div><div>E</div>C = 0</div> <div><div>P</div>D = 0</div> <div><div>▽</div> = 0</div> <div><div>C</div> = 0</div> <div><div>⊠</div> = 0</div> <div><div>■</div> = 0</div> <div><div>▽</div> = 0</div>						MM		1:15											
						ANGULAR TOL ± °		DRWN BY		DATE									
						4 PLACES ±		KSAMIEC		2017/05/03									
						3 PLACES ±		CHK'D BY		DATE									
						2 PLACES ± 0.25		CHKD BY											
						1 PLACE ± 0.15		APPR BY		DATE									
						0 PLACES ± 0.0		FSMITH		2017/06/16									
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION									
								B											
		A1		REV						SERIES		MATERIAL NUMBER		CUSTOMER					
										70058									
												DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
												700580000-SD		PSD		000		4 OF 4	