



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE1428

Integrated Circuit

Cylinder Servo Control Circuit for VCR

Description:

The NTE1428 is an integrated circuit designed for VTR's cylinder servo control.

Features:

- Sample Hold System Speed Control
- Incorporating Recording/Playback Switching Circuit
- Supply Voltage Either 9V or 12V

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Supply Voltage, V_{1-7} 14.4V
Power Dissipation, P_D 880mW
Operation ambient temperature, T_{opr} -20 to $+70^\circ\text{C}$
Storage temperature, T_{stg} -40 to $+150^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter		Symbol	Test Conditions	Min	Typ	Max	Unit
Circuit Current		I_1	$V_{1-7} = 12\text{V}$	33	–	65	mA
Sensitivity	PG – Amp. In	$S_{(1)}$	$V_{CC} = 12\text{V}$, 30Hz duty 96%	1	–	–	V_{o-p}
	PG + Amp. In	$S_{(2)}$	$V_{CC} = 12\text{V}$, 30Hz duty 4%	1	–	–	V_{o-p}
	Cap PG Amp. In	$S_{(3)}$	$V_{CC} = 12\text{V}$	50	–	–	m V_{o-p}
	V_{SS} Amp. In	$S_{(4)}$		2	–	–	V_{o-p}
	REF Amp. In	$S_{(5)}$		3	–	–	V_{o-p}
	REC/P.B. Switch	$S_{(6)}$		5	–	–	V
Ref. Voltage (phase trapezoidal wave)		$V_{REF(1)}$		2.7	–	3.7	V
High-level output Voltage (Head-SW)		$V_{OH(1)}$	$V_{CC} = 12\text{V}$, $V_{I24} = 2V_{p-p}$, 30Hz duty 4%	9	–	–	V
Low-level output Voltage (Head-SW)		$V_{OL(2)}$		–	–	600	mV
High-level output Voltage (REC CTL Amp)		$V_{OH(2)}$	$V_{CC} = 12\text{V}$	8	–	–	V
Low-level output Voltage (REC CTL Amp)		$V_{OL(2)}$		–	–	1	V
High-level output Voltage (S/H1)		$V_{OH(3)}$		9	–	–	V
Low-level output Voltage (S/H1)		$V_{OL(3)}$		–	–	600	mV
Voltage Gain (CTL Amp.)		G_V		62	–	70	dB
Sensitivity (FG Amp. In)		$S_{(7)}$		100	–	–	m V_{p-p}
Ref. Voltage (speed system trapezoidal wave)		$V_{REF(2)}$		2.7	–	3.7	V

Electrical Characteristics (Cont'd): ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
High-level output Voltage (S/H2)	$V_{OH(4)}$	$V_{CC} = 12\text{V}$	10	–	–	V
Low-level output Votlage (S/H2)	$V_{OL(4)}$		–	–	1.8	V
High-level output Voltage (Cap PG)	$V_{OH(5)}$		4.4	–	6.6	V
Low-level output Voltage (Cap PG)	$V_{OL(5)}$		–	–	600	mV

Pin Connection Diagram

