


注記
NOTE

- △ 全極数が偶数の場合のみ適用。
TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.
- 2 ウエハーの反りは、長さ 25.4 に対して 0.2 最大。
CAMBER MUST BE 0.2 MAX. PER 25.4.



50.72	47.52	09-67-4122	5275-12A	12
46.76	43.56	↑ -4112	↑ -11A	11
42.8	39.6	↑ -4102	↑ -10A	10
38.84	35.64	↑ -4092	↑ -09A	9
34.88	31.68	↑ -4082	↑ -08A	8
30.92	27.72	↑ -4072	↑ -07A	7
26.96	23.76	↑ -4062	↑ -06A	6
23	19.8	↑ -4052	↑ -05A	5
19.04	15.84	↑ -4042	↑ -04A	4
15.08	11.88	↑ -4032	↑ -03A	3
11.12	7.92	09-67-4022	5275-02A	2
B	A	EDP NO.	ENG. NO.	極数 CKT.

角度 ANGLE	±3°					材料 MATERIAL	図中参照 SEE DRAWING
30 以上 OVER	±0.3					仕上げ FINISH	—H—
10 以上 30 未満 OVER UNDER	±0.25	C	変更 REVISED	(JC60666)	T.Y.	適用電線範囲 WIRE RANGE	—H—
10 未満 UNDER	±0.2	B	変更 & 再作図 REVISED & REDRAWN	(J40818)	T.A.	被覆外径 INS. RANGE	—H—
一般公差 GENERAL TOLERANCES		記号 LTR	変更内容 REVISION RECORD	DR.	日付 DATE	DRAWN BY T.ASAKAWA	CHK'D BY S.A. S.KUNISHI
				CHK.		APP'D BY S.KUNISHI	尺 SCALE

molex MOLEX-JAPAN CO.,LTD.
日本モレックス株式会社

REVISE ONLY ON CAD SYSTEM

TITLE 名称
KK 3.96/7.92
WAFER ASS'Y

DWG. NO.

SD-5275-NA

REV

C