

Class AB stereo headphone driver

TDA1308

FEATURES

- Wide temperature range
- No switch ON/OFF clicks
- Excellent power supply ripple rejection
- Low power consumption
- Short-circuit resistant
- High performance
 - high signal-to-noise ratio
 - high slew rate
 - low distortion
- Large output voltage swing.

GENERAL DESCRIPTION

The TDA1308 is an integrated class AB stereo headphone driver contained in an SO8 or a DIP8 plastic package. The device is fabricated in a 1 mm CMOS process and has been primarily developed for portable digital audio applications.

QUICK REFERENCE DATA

$V_{DD} = 5\text{ V}$; $V_{SS} = 0\text{ V}$; $T_{amb} = 25\text{ °C}$; $f_i = 1\text{ kHz}$; $R_L = 32\text{ }\Omega$; unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
V_{DD}	supply voltage single dual		3.0	5.0	7.0	V
			1.5	2.5	3.5	V
V_{SS}	negative supply voltage		–1.5	–2.5	–3.5	V
I_{DD}	supply current	no load	–	3	5	mA
P_{tot}	total power dissipation	no load	–	15	25	mW
P_o	maximum output power	THD < 0.1%; note 1	–	60	–	mW
(THD + N)/S	total harmonic distortion plus noise-to-signal ratio	note 1				
			–	0.03	0.06	%
			–	–70	–65	dB
		$R_L = 5\text{ k}\Omega$	–	–101	–	dB
S/N	signal-to-noise ratio		100	110	–	dB
α_{cs}	channel separation		–	70	–	dB
		$R_L = 5\text{ k}\Omega$	–	105	–	dB
PSRR	power supply ripple rejection	$f_i = 100\text{ Hz}$; $V_{ripple(p-p)} = 100\text{ mV}$	–	90	–	dB
T_{amb}	operating ambient temperature		–40	–	+85	°C

Note

1. $V_{DD} = 5\text{ V}$; $V_{O(p-p)} = 3.5\text{ V}$ (at 0 dB).


ORDERING INFORMATION

TYPE NUMBER	PACKAGE		
	NAME	DESCRIPTION	VERSION
TDA1308	DIP8	plastic dual in-line package; 8 leads (300 mil)	SOT97-1
TDA1308T	SO8	plastic small outline package; 8 leads; body width 3.9 mm	SOT96-1

Class AB stereo headphone driver


TDA1308

BLOCK DIAGRAM



PINNING

SYMBOL	PIN	DESCRIPTION
OUTA	1	output A
INA(neg)	2	inverting input A
INA(pos)	3	non-inverting input A
Vss	4	negative supply
INB(pos)	5	non-inverting input B
INB(neg)	6	inverting input B
OUTB	7	output B
VDD	8	positive supply



TDA1308




Fig.3 Equivalent schematic diagram.

Class AB stereo headphone driver

TDA1308

LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V_{DD}	supply voltage		0	8.0	V
$t_{SC(O)}$	output short-circuit duration	$T_{amb} = 25\text{ }^{\circ}\text{C}$; $P_{tot} = 1\text{ W}$	20	—	s
T_{stg}	storage temperature		−65	+150	$^{\circ}\text{C}$
T_{amb}	operating ambient temperature		−40	+85	$^{\circ}\text{C}$
V_{esd}	electrostatic discharge	note 1	−2000	+2000	V
		note 2	−200	+200	V

Notes

- Human body model: $C = 100\text{ pF}$; $R = 1500\text{ }\Omega$; 3 pulses positive plus 3 pulses negative.
- Machine model: $C = 200\text{ pF}$; $L = 0.5\text{ mH}$; $R = 0\text{ }\Omega$; 3 pulses positive plus 3 pulses negative.

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	VALUE	UNIT
$R_{th\ j-a}$	thermal resistance from junction to ambient in free air		
	DIP8	109	K/W
	SO8	210	K/W

QUALITY SPECIFICATION

In accordance with "UZW-BO/FQ-0601". The numbers of the quality specification can be found in the "Quality Reference Handbook". The handbook can be ordered using the code 9398 510 63011.

Class AB stereo headphone driver

TDA1308

CHARACTERISTICS

 $V_{DD} = 5\text{ V}$; $V_{SS} = 0\text{ V}$; $T_{amb} = 25\text{ }^{\circ}\text{C}$; $f_i = 1\text{ kHz}$; $R_L = 32\text{ }\Omega$; unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
Supplies						
V_{DD}	supply voltage					
	single		3.0	5.0	7.0	V
	dual		1.5	2.5	3.5	V
V_{SS}	negative supply voltage		-1.5	-2.5	-3.5	V
I_{DD}	supply current	no load	–	3	5	mA
P_{tot}	total power dissipation	no load	–	15	25	mW
DC characteristics						
$V_{I(0s)}$	input offset voltage		–	10	–	mV
I_{bias}	input bias current		–	10	–	pA
V_{CM}	common mode voltage		0	–	3.5	V
G_v	open-loop voltage gain	$R_L = 5\text{ k}\Omega$	–	70	–	dB
I_O	maximum output current	$(THD + N)/S < 0.1\%$	–	60	–	mA
R_O	output resistance		–	0.25	–	Ω
V_O	output voltage swing	note 1	0.75	–	4.25	V
		$R_L = 16\text{ }\Omega$; note 1	1.5	–	3.5	V
		$R_L = 5\text{ k}\Omega$; note 1	0.1	–	4.9	V
PSRR	power supply rejection ratio	$f_i = 100\text{ Hz}$; $V_{ripple(p-p)} = 100\text{ mV}$	–	90	–	dB
α_{cs}	channel separation		–	70	–	dB
		$R_L = 5\text{ k}\Omega$	–	105	–	dB
C_L	load capacitance		–	–	200	pF
AC characteristics						
(THD + N)/S	total harmonic distortion plus noise-to-signal ratio	note 2	–	–70	–65	dB
			–	0.03	0.06	%
		note 2; $R_L = 5\text{ k}\Omega$	–	–101	–	dB
			–	0.0009	–	%
S/N	signal-to-noise ratio		100	110	–	dB
f_G	unity gain frequency	open-loop; $R_L = 5\text{ k}\Omega$	–	5.5	–	MHz
P_O	maximum output power	$(THD + N)/S < 0.1\%$	–	60	–	mW
C_i	input capacitance		–	3	–	pF
SR	slew rate	unity gain inverting	–	5	–	V/ μ s
B	power bandwidth	unity gain inverting	–	20	–	kHz

Notes

- Values are proportional to V_{DD} ; $(THD + N)/S < 0.1\%$.
- $V_{DD} = 5.0\text{ V}$; $V_{O(p-p)} = 3.5\text{ V}$ (at 0 dB).

Class AB stereo headphone driver

TDA1308

TEST AND APPLICATION INFORMATION




Fig.4 Measurement circuit for inverting application.




Fig.5 Example of application with TDA1545A (stereo continuous calibration DAC).

Class AB stereo headphone driver

TDA1308




Fig.6 Open-loop gain as a function of input frequency.




Fig.7 Crosstalk as a function of input frequency.




Fig.8 Output power as a function of supply voltage.

Class AB stereo headphone driver

TDA1308




Fig.9 Total harmonic distortion plus noise-to-signal ratio as a function of input frequency.




Fig.10 Total harmonic distortion plus noise-to-signal ratio as a function of output voltage level.