




 CLOSED
 GESCHLOSSEN

 OPEN
 OFFEN


CABLE

PVC round cable LIYY 2x0.14mm², 350V
 colour grey, colour of wires brown/white
 ends 5±1 mm stripped and tinned

PVC Rundkabel LIYY 2x0.14 mm², 350V
Mantelfarbe grau, Aderfarben braun/weiß
Enden 5±1 mm abisoliert und verzinkt

MATERIAL

stem- polypropylene white
 nut- polypropylene white
 float- polypropylene white
 O-ring- nitril cautchuk black

Schaft- Polypropylen weiss
Mutter- Polypropylen weiss
Schwimmer- Polypropylen weiss
O-Ring nitril Kautschuk schwarz

Float specific density - approx. 0.7 g/cm³
Spezifisches Schwimmergewicht ca. 0.7 g/cm³

MARKING

MEDER-Label, Typ
 Production code EN60062/
 Factory code

MEDER-Logo, Typ
Produktionscode
EN60062/Fertigungsstätte



dimensions / Abmessungen (mm)
 unspecified tolerances acc. to DIN ISO 2768-m

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
operating voltage	DC or Peak AC			250	VDC
operating ampere	DC or Peak AC			1	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive			290	mOhm
Housing material		PP			
Case color		white			
Sealing compound		Polyurethan			

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature	Not including cable	-30		80	°C
Operating temperature	including cable	-5		80	°C
Storage temperature		-30		80	°C
safety class	DIN EN 60529	IP68, until the thread			

Cable specification	Conditions	Min	Typ	Max	Unit
Cable typ		round cable			
Cable material		PVC			
Cross section		0,14 qmm			

General data	Conditions	Min	Typ	Max	Unit
Mounting advice		over 5m cable, a series resistor is recommended.			
Tightening torque				3	Nm