











RECOMMENDED P.C.B. LAYOUT (T=1.6mm/2.0mm/2.4mm)



SECTION A-A



SECTION B-B



SECTION C-C

NOTES:

1. MATERIAL:

HOUSING: THERMAL PLASTIC, UL94V-0, COLOR: SEE SHEET2
TERMINAL/PEG: COPPER ALLOY, THICKNESS=0.25MM

2. TERMINAL PLATING:

CONTACT AREA: (a) GOLD FLASH
(b) 0.76 MICRON GOLD PLATED
(c) 0.38 MICRON GOLD PLATED

SOLDER TAIL:

1.27 MICRON MIN. MATTE TIN PLATED

UNDER PLATE:

1.27 MICRON MIN. NICKEL PLATED

3. PEG PLATING:


1.27 MICRON MIN. MATTE TIN PLATED OVERALL
1.27 MICRON MIN. NICKEL UNDER PLATED

4. PACKAGING SPECIFICATION REFER TO PK-67491-001

5. PRODUCT SPECIFICATION REFER TO PS-67491-001

6. MATING PART: 67489

7. RECOMMENDED PROCESS: WAVE SOLDERING



OBSOLETE PARTS EC NO: SH2011-0104 DRW:GLLI CHKD: APPR:RZHANG REV		QUALITY SYMBOLS F_A=0 F_B=0 F_C=0		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm		INCH		DRAWN BY DATE		TITLE 1.27MM HIGH SPEED PLUG VERTICAL TYPE			
				4 PLACES ± --- ± ---		GRATE MA 2004/02/02							
				3 PLACES ± --- ± ---		CHECKED BY DATE		MOLEX INCORPORATED					
				2 PLACES ± 0.15 ± ---		YAJUN 2004/02/02							
				1 PLACE ± 0.25 ± ---		APPROVED BY DATE		DOCUMENT NO. SD-67491-001					
				ANGULAR ± 3 °		RZHANG 2010/11/03							
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NO.		SHEET NO. 1 OF 2			
								SEE CHART IN SHEET 2					
								SIZE A3					
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													

[illegible]