


Model 6082
Elastic Wrist Strap with Clip & Cord



Materials

Wrist Strap:

Body – Impact resistant plastic
Strap – Elastic Fibers with Silver Plated Nylon yarn.
Circumference: 2.50" (64,0) min., 13.00" (330,0) max.

Snap and Cam – Stainless Steel

Ground Cord:

Banana Plug:

Body – Brass, Nickel-plated
Insulation – PVC, Black

Cord:

Material – Coiled Tinsel
Insulation – Polyurethane 2.25mm O.D.
Length: 6 feet, extended

Snap (4mm):

Body – Brass, Nickel-plated, 0.12" (3,2) I.D.
Insulation – PVC, Black



Features

- A complete wrist strap kit features the adjustable fabric wrist strap.
- Also included: Resistive Coiled Cord (1 Megohm resistor molded in) extendable to 6 feet with a Straight Banana Plug and Alligator Clip.

Ordering Information

Model: 6082

Packaging: Elastic Strap, Ground Cord, Alligator Clip, and Instruction Sheet per bag.

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.