

UP04979

Silicon N-channel MOSFET (Tr1)
Silicon P-channel MOSFET (Tr2)

For switching

■ Features

- High-speed switching
- Gate protection diode built-in
- Two elements incorporated into one package
(Each transistor is separated)
- Reduction of the mounting area and assembly cost by one half


■ Basic Part Number

- 2SJ0672 + 2SK3539

■ Absolute Maximum Ratings $T_a = 25^\circ\text{C}$


Parameter	Symbol	Rating	Unit
Tr1	Drain-source surrender voltage	V_{DSS}	50
	Gate-source voltage (Drain open)	V_{GSO}	± 7
	Drain current	I_D	mA
	Peak drain current	I_{DP}	mA
Tr2	Drain-source surrender voltage	V_{DSS}	-30
	Gate-source voltage (Drain open)	V_{GSO}	± 7
	Drain current	I_D	-100 mA
	Peak drain current	I_{DP}	-200 mA
Overall	Total power dissipation *	P_T	mW
	Junction temperature	T_{ch}	$^\circ\text{C}$
	Storage temperature	T_{stg}	-55 to +125 $^\circ\text{C}$

Note) *: Measuring on substrate at 17 mm \times 10 mm \times 1 mm



Marking Symbol: 4T

Internal Connection



■ Electrical Characteristics $T_a = 25^\circ\text{C} \pm 3^\circ\text{C}$

• Tr1

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Drain-source surrender voltage	V_{DSS}	$I_D = 10 \mu\text{A}, V_{GS} = 0$	50			V
Drain-source cutoff current	I_{DSS}	$V_{DS} = 30 \text{ V}, V_{GS} = 0$			1.0	μA
Gate-source cutoff current	I_{GSS}	$V_{GS} = \pm 7 \text{ V}, V_{DS} = 0$			± 10	μA
Gate threshold voltage	V_{th}	$I_D = 1.0 \mu\text{A}, V_{DS} = 3.0 \text{ V}$	0.5	1.0	1.5	V
Drain-source ON resistance	$R_{DS(on)}$	$I_D = 10 \text{ mA}, V_{GS} = 2.5 \text{ V}$		8	15	Ω
		$I_D = 10 \text{ mA}, V_{GS} = 4.0 \text{ V}$		6	12	
Forward transfer admittance	$ Y_{fs} $	$I_D = 10 \text{ mA}, V_{DS} = 3.0 \text{ V}$	20	60		mS
Turn-on time *	t_{on}	$V_{DD} = 3 \text{ V}, V_{GS} = 0 \text{ V} \text{ to } 3 \text{ V}, I_D = 10 \text{ mA}$		200		ns
Turn-off time *	t_{off}	$V_{DD} = 3 \text{ V}, V_{GS} = 3 \text{ V} \text{ to } 0 \text{ V}, I_D = 10 \text{ mA}$		200		ns

Note) 1. Measuring methods are based on JAPANESE INDUSTRIAL STANDARD JIS C 7030 measuring methods for transistors.

2. *: Refer to t_{on} , t_{off} test circuit.


• Tr2

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Drain-source surrender voltage	V_{DSS}	$I_D = -10 \mu\text{A}, V_{GS} = 0$	-30			V
Drain-source cutoff current	I_{DSS}	$V_{DS} = -20 \text{ V}, V_{GS} = 0$			-1.0	μA
Gate-source cutoff current	I_{GSS}	$V_{GS} = \pm 7 \text{ V}, V_{DS} = 0$			± 10	μA
Gate threshold voltage	V_{th}	$I_D = -1.0 \mu\text{A}, V_{DS} = -3.0 \text{ V}$	-0.5	-1.0	-1.5	V
Drain-source ON resistance	$R_{DS(on)}$	$I_D = -10 \text{ mA}, V_{GS} = -2.5 \text{ V}$		25	45	Ω
		$I_D = -10 \text{ mA}, V_{GS} = -4.0 \text{ V}$		15	30	
Forward transfer admittance	$ Y_{fs} $	$I_D = -10 \text{ mA}, V_{DS} = -3.0 \text{ V}$	20	35		mS
Turn-on time *	t_{on}	$V_{DD} = -3 \text{ V}, V_{GS} = 0 \text{ V} \text{ to } -3 \text{ V}, I_D = -10 \text{ mA}$		850		ns
Turn-off time *	t_{off}	$V_{DD} = -3 \text{ V}, V_{GS} = -3 \text{ V} \text{ to } 0 \text{ V}, I_D = -10 \text{ mA}$		850		ns


Note) 1. Measuring methods are based on JAPANESE INDUSTRIAL STANDARD JIS C 7030 measuring methods for transistors.

2. *: Refer to t_{on} , t_{off} test circuit.


t_{on} , t_{off} test circuit (Tr1)








t_{on} , t_{off} test circuit (Tr2)







Common characteristics chart



Characteristics charts of Tr1



Characteristics charts of Tr2



Request for your special attention and precautions in using the technical information and semiconductors described in this material

(1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technical information described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.

(2) The technical information described in this material is limited to showing representative characteristics and applied circuits examples of the products. It neither warrants non-infringement of intellectual property right or any other rights owned by our company or a third party, nor grants any license.

(3) We are not liable for the infringement of rights owned by a third party arising out of the use of the technical information as described in this material.

(4) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).

Consult our sales staff in advance for information on the following applications:

- Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
- Any applications other than the standard applications intended.

(5) The products and product specifications described in this material are subject to change without notice for modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.

(6) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage, and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.

Even when the products are used within the guaranteed values, take into the consideration of incidence of break down and failure mode, possible to occur to semiconductor products. Measures on the systems such as redundant design, arresting the spread of fire or preventing glitch are recommended in order to prevent physical injury, fire, social damages, for example, by using the products.

(7) When using products for which damp-proof packing is required, observe the conditions (including shelf life and amount of time let standing of unsealed items) agreed upon when specification sheets are individually exchanged.

(8) This material may be not reprinted or reproduced whether wholly or partially, without the prior written permission of Matsushita Electric Industrial Co., Ltd.