

## SL Series • Toroidal Power Inductors

### Features

- Operating frequency to 1MHz
- High energy storage with minimum saturation
- High stability from no load to full load
- Available in both SMD and TH versions
- Manufactured in ISO 9001:2015 and ISO 14001:2015 certified Talema facility
- Meets lead free reflow level J-STD-020C
- Fully RoHS & REACH Compliant



### Electrical Specifications @25°C

Test frequency: Inductance measured @10KHz / 10mV

Test voltage between windings: 500Vrms

Operating temperature range: -40°C to +130°C


Climatic Category: IEC68-1 40/125/56

Part Number	Rated Current (I <sub>DC</sub> )	L <sub>N</sub> (μH) @ I rated ±20%	L <sub>O</sub> (μH) No Load ±20%	DCR (mOhms) Nominal	Energy Storage (μJ)	Package	
						"SMD"	"THT"
SL_-3.4-1.01	3.40	1.01	1.10	9.6	6	S1	T1
SL_-1.4-6.2	1.40	6.20	7.00	62.0	6	S1	T1
SL_-1.0-17.6	1.00	17.60	23.96	117.7	9	S1	T1
SL_-4.8-3.8	4.80	3.80	5.20	17.0	44	S2	T2
SL_-2.8-9.4	2.80	9.40	12.20	41.1	37	S2	T2
SL_-1.4-29.7	1.40	29.70	35.30	144.3	29	S2	T2
SL_-0.94-114	0.94	114.00	167.00	411.2	50	S2	T2
SL_-8.0-2.5	8.00	2.50	3.80	7.8	80	S3	T3
SL_-5.4-5.1	5.40	5.10	7.50	17.5	74	S3	T3
SL_-2.7-16.2	2.70	16.20	21.90	68.5	59	S3	T3
SL_-1.3-58.1	1.30	58.10	73.00	288.8	49	S3	T3
SL_-0.9-192	0.90	192.00	292.00	534.7	78	S3	T3
SL_-0.72-383	0.72	383.00	674.00	765.0	99	S3	T3
SL_-7.8-4.9	7.80	4.90	7.90	10.9	149	S4	T4
SL_-5.5-9.0	5.50	9.00	14.00	26.1	136	S4	T4
SL_-2.7-29.1	2.70	29.10	40.50	93.8	106	S4	T4
SL_-0.74-645	0.74	645.00	1134.00	1267.2	177	S4	T4
SL_-14.3-0.81	14.30	0.81	1.25	2.3	83	SH3	--
SL_-11.5-1.32	11.50	1.32	2.10	3.2	87	SH3	--
SL_-13.9-1.68	13.90	1.68	2.80	3.3	162	SH4	--
SL_-11.4-2.5	11.40	2.50	4.20	4.9	162	SH4	--
SL_-7.2-9.3	7.20	9.30	16.00	15.1	241	S5	T5
SL_-5.1-16.1	5.10	16.10	25.90	27.3	209	S5	T5
SL_-2.6-50.0	2.60	50.00	72.90	117.2	169	S5	T5
SL_-0.71-1070	0.71	1070.00	1950.00	1616.1	270	S5	T5
SL_-12.4-3.5	12.40	3.50	6.50	5.9	269	SH5	--
SL_-10.4-4.7	10.40	4.70	8.40	7.1	254	SH5	--
SL_-15.4-5.2	15.40	5.20	10.30	5.5	617	SH6A	TH6A
SL_-10.9-9.4	10.90	9.40	17.60	11.3	558	SH6A	TH6A
<b>Coupled Inductors</b>							
SLC_-1.1-43.6	1.10	43.60	70.30	280.7	26	SC3	TC3
SLC_-2.7-21.9	2.70	21.90	42.90	81.0	80	SC4	--
SLC_-6.4-4.03	6.40	4.03	6.50	19.0	82	SC5	TC5
SLC_-23.8-0.53	23.80	0.53	0.88	1.2	150	SHC4	--
SLC_-21-1.1	21.00	1.10	2.10	2.1	243	SHC5	--
SLC_-22.4-2.1	22.40	2.10	4.00	3.1	527	SHC6	THC6


**Note:** The inductance values listed above are based on a 55°C temperature rise and 25°C ambient temperature.

## Mounting Styles • SL Series Toroidal Power Inductors



### Type S1 - S5




#### Suggested Pad Layout






#### Schematic




### Type T1 - T5




#### Suggested Board Layout (Top Side View)





### Type SH3 - SH6A







#### Suggested Pad Layout



#### Schematic





### Type TH6A





## Coupling Transformers

### Type SC3 - SC5

#### Suggested Pad Layout





### Type SC4




### Type TC3 & TC5


#### Suggested Pad Layout



#### Schematic



## Mounting Styles • SL Series Toroidal Power Inductors



**Note:**

When ordering, add "S" or "T" to the basic part number to denote preferred mounting style.

**Example:** SLS-3.4-1.03 for SMD or SLT-3.4-1.03 for through hole mounting.

Mounting Style	Size Code	Dimensions - Inches $\pm 0.010$ (mm $\pm 0.25$ )				
		A	B	C	D	E
"S"	S1	0.339 (8.60)	0.339 (8.60)	0.220 (5.60)	0.268 (6.90)	0.354 (9.00)
	S2	0.433 (11.00)	0.441 (11.20)	0.303 (7.70)	0.358 (9.10)	0.413 (10.50)
	S3	0.551 (14.00)	0.559 (14.20)	0.343 (8.70)	0.461 (11.70)	0.520 (13.20)
	S4	0.591 (15.00)	0.614 (15.60)	0.390 (9.90)	0.508 (12.90)	0.551 (14.00)
	S5	0.669 (17.00)	0.701 (17.80)	0.441 (11.20)	0.591 (15.00)	0.630 (16.00)
"SH"	SH3	0.620 (15.75)	0.605 (15.37)	0.370 (9.40)	0.500 (12.70)	0.500 (12.70)
	SH4	0.670 (17.02)	0.670 (17.02)	0.390 (9.90)	0.560 (14.22)	0.490 (12.45)
	SH5	0.740 (18.80)	0.740 (18.80)	0.390 (9.90)	0.630 (16.00)	0.640 (16.26)
	SH6A	0.925 (23.50)	0.957 (24.30)	0.445 (11.30)	0.843 (21.40)	0.728 (18.50)
"SC"	SC3	0.551 (14.00)	0.630 (16.00)	0.343 (8.70)	0.530 (13.46)	0.348 (8.84)
	SC4	0.590 (14.99)	0.715 (18.16)	0.390 (9.91)	0.600 (15.24)	0.370 (9.40)
	SC5	0.662 (16.82)	0.760 (19.31)	0.413 (10.50)	0.660 (16.76)	0.445 (11.30)
"SHC"	SHC4	0.715 (18.16)	0.865 (21.97)	0.390 (9.91)	0.760 (19.30)	0.360 (9.14)
	SHC5	0.800 (20.32)	0.910 (23.11)	0.390 (9.91)	0.800 (20.32)	0.440 (11.18)
	SHC6	1.000 (25.40)	1.104 (28.05)	0.409 (10.40)	1.010 (25.65)	0.620 (15.75)

Mounting Style	Size Code	Dimensions - Inches $\pm 0.010$ (mm $\pm 0.25$ )					Lead $\varnothing$
		A	B	C	D	E	
"T"	T1	0.339 (8.60)	0.339 (8.60)	0.201 (5.10)	0.250 (6.35)	0.250 (6.35)	0.020 (0.50)
	T2	0.433 (11.00)	0.441 (11.20)	0.280 (7.10)	0.300 (7.62)	0.300 (7.62)	0.020 (0.50)
	T3	0.551 (14.00)	0.559 (14.20)	0.311 (7.90)	0.375 (9.52)	0.375 (9.52)	0.020 (0.50)
	T4	0.591 (15.00)	0.614 (15.60)	0.358 (9.10)	0.300 (7.62)	0.500 (12.70)	0.022 (0.55)
	T5	0.669 (17.00)	0.701 (17.80)	0.409 (10.40)	0.600 (15.24)	0.500 (12.70)	.026 (0.65)
"TH"	--	--	--	--	--	--	--
	--	--	--	--	--	--	--
	--	--	--	--	--	--	--
	TH6A	0.925 (23.50)	0.957 (24.30)	0.386 (9.80)	0.650 (16.51)	0.800 (20.32)	0.031 (0.80)
"TC"	TC3	0.551 (14.00)	0.630 (16.00)	0.327 (8.30)	0.500 (12.70)	0.400 (10.16)	0.024 (0.60)
	--	--	--	--	--	--	--
	TC5	0.662 (16.82)	0.760 (19.31)	0.362 (9.20)	0.500 (12.70)	0.500 (12.70)	0.024 (0.60)
"THC"	--	--	--	--	--	--	--
	THC6	1.000 (25.40)	1.104 (28.05)	0.357 (9.08)	1.000 (25.40)	0.600 (15.24)	0.028 (0.70)

**Regional Locations - Design, Manufacturing, Sales & Marketing**

**Talema Group Regional Offices**

**North America**

**United States  
(Sales & Marketing)**

**Talema Group, LLC**  
 PO Box 935  
 900 Innovation Drive  
 Suite 120, Rolla  
 Missouri 65402  
 Tel: +1 573-303-3675  
 E-Mail:  
[sales@talemagroup.com](mailto:sales@talemagroup.com)  
 Web: [www.talema.com](http://www.talema.com)

**Asia**

**India  
(Design, Manufacturing, Sales & Marketing)**

**Administrative Office**  
**Talema Electronic India Private Limited**  
 Door No. 221, 1st and 2nd Floor  
 KJ Plaza, Opp.to Vidya Mandir School  
 Meyanoor Main Road  
 Salem - 636 004 Tamil Nadu INDIA  
 Tel: +91 427 - 243 3100  
 Fax: +91 427 - 243 3109  
 E-Mail: [talema@talemaindia.net](mailto:talema@talemaindia.net)  
 Web: [www.talema.com](http://www.talema.com)

**Factory Premises**  
**Talema Electronic India Private Limited**  
 Plot Nos. 30, 31 Electrical and Electronic  
 Industrial Estate  
 Suramangalam  
 Salem - 636 005 Tamil Nadu INDIA  
 Tel: +91 427 - 243 3000  
 E-Mail: [talema@talemaindia.net](mailto:talema@talemaindia.net)  
 Web: [www.talema.com](http://www.talema.com)

**Europe**

**Germany  
(Design, Sales & Marketing)**

**Talema Elektronik GmbH**  
 Sembdnerstr. 5  
 82110 Germering  
 Tel: +49 89 - 841 00 - 0  
 Fax: +49 89 - 841 00 25  
 E-Mail: [info@talema.de](mailto:info@talema.de)  
 Web: [www.talema.com](http://www.talema.com)

**Ireland  
(Design, Sales & Marketing)**

**Nuvotem TEO**  
 Units W & X, Gweedore Business Park  
 Derrybeg, Letterkenny, Co. Donegal  
 Tel: +353 (0) 74 95 48666  
 Fax: +353 (0) 74 95 48139  
 E-Mail: [info@nuvotem.com](mailto:info@nuvotem.com)  
 Web: [www.nuvotem.com](http://www.nuvotem.com)

**Czech Republic  
(Design, Manufacturing, Sales & Marketing)**

**NT Magnetics s.r.o.**  
 Chebská 27  
 322 00 Plzeň  
 Tel: +420 377 - 338 351  
 Fax: +420 377 - 338 350  
 E-Mail: [talema@talema.cz](mailto:talema@talema.cz)  
 Web: [www.ntmagnetics.cz](http://www.ntmagnetics.cz)

**Locations of Talema Group Regional Offices**

