



PROJECT NO.:		REVISIONS				
PRJ-11-000004377		ÄNDERUNGEN		DATE	DWN	APVD
P	LYR	DESCRIPTION				
		BESCHREIBUNG				
	A	NEW RELEASE		04DEC2014	TJ	PS



TECHNICAL DATA	2-2172067-2	3-2172067-2
RATED VOLTAGE	60V	30V
RATED IMPULSE VOLTAGE	800V	800V
POLLUTION DEGREE	3	3
OVERVOLTAGE CATEGORY	II	II
MATERIAL GROUP	II	II
RATED CURRENT	4A	4A
VOLUME RESISTIVITY	≤ 3mΩ	≤ 3mΩ
DEGREE OF PROTECTION	IP67	IP67
UPPER TEMPERATURE	+85 °C	+85 °C
LOWER TEMPERATURE	-40 °C	+40 °C






PIN ARRANGEMENT

2-2172067-2

3-2172067-2



CONDUCTOR LAYOUT



NOTES

- 1 MATERIAL: ITEM NO. 1: CONTACT BODY - PA
ITEM NO. 2: CONTACT - CuZn (BRASS)
CONTACT FINISH - Au (GOLD)
- 2 ALL DIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).		DWN YASHKUMAR 25JUL2014
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		CHK M. BRUBAKER 25JUL2014
DIMENSIONS: MASSEINHEIT: ITMM		APVD M. BRUBAKER 25JUL2014
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		PRODUCT SPEC 108-19483
0 PLC ±		APPLICATION SPEC 114-32127
1 PLC ±		WEIGHT -
2 PLC ±		Customer Drawing
3 PLC ±		
4 PLC ±		
ANGLES/WINKEL ±		
FINISH/OBERFLÄCHE/FARBE		
MATERIAL		
SEE NOTES		

1	4	3-2172067-2
1	3	2-2172067-2
MATERIAL	NUMBER OF POLES	TE-PART-NO.

TE Connectivity

M8 RECEPTACLE, MALE, PCB MOUNT, ANGLED

SIZE A2	CAGE CODE 00779	DRAWING NO. C-2172067	RESTRICTED TO MUR FÜR -
SCALE MASSSTAB 5:1	SHEET BLATT 1	OF 1	REV A