



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AJ	16		B	REVISED PER ECO 07-002853	21MAR2007	DW JL



- 1 ZINC PER QQ-Z-363.
- 2 BERYLLIUM COPPER PER ASTM-B-643
- 3 PTFE PER MIL-P-19468.
- 4 COPPER-IRON ALLOY PER ASTM-B-465.
- 5 COPPER PER QQ-C-576.
- 6 COPPER ALLOY PER ASTM-B-122.
- 7 NICKEL PLATE PER QQ-N-290
3.81µm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204
0.76µm [.000030] MINIMUM THICK.
- 9 TIN PLATE PER ASTM-B-545,
2.54 µm [.000100] MIN THICK.
- 10 GOLD PLATE PER MIL-G-45204
- 11 CONNECTOR PRESS FIT IS DESIGNED TO PROVIDE 100 LB. MINIMUM AXIAL RETENTION TO PCB COMPLIANT WITH TYCO APPLICATION SPEC 114-12001. AS A RESULT, DEFORMATION OF PLATED THROUGH HOLES WILL OCCUR. CUSTOMER VALIDATION AND ACCEPTANCE OF THIS DEFORMATION IS RECOMMENDED PRIOR TO SPECIFYING USE OF THIS PRODUCT.



PCB CONFIGURATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA CHK J. HAVENER APVD J. LIPPERT	21APR2005 DOCK5 21APR2005 21APR2005	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-12103 APPLICATION SPEC 114-12001		NAME JACK, PCB, HIGH RETENTION PRESS FIT, 50 OHM, BNC		SIZE A2	CAGE CODE 00779
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.05 [.002] 3 PLC ± - 4 PLC ± - ANGLES ± -	WEIGHT -		DRAWING NO C=5222006		RESTRICTED TO -	
	FINISH SEE NOTES 7-10	CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV B	