






11	FINISH: 0.00002[.000001] MIN GOLD ON GOLD PLATED AREA, 0.00381-0.00635[.000150-.000250] MATTE TIN ON TIN PLATE AREA, UNDERPLATING TO BE 0.00127-0.00254[.000050-.000100] NICKEL ON ENTIRE CONTACT, GOLD AND TIN PLATING MAY NOT OVERLAP.
12	OBSOLETE



DETAIL R

4805 (3/11)

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOCAD

DIST00

REV

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

—

—

—

11

27.79
[1.094]

20.32
[.800]

15

24.89
[.980]

34

8

8-104666-3

12.55
[.494]

5.08
[.200]

4

9.65
[.380]

10

8

8-104666-2

22.71
[.894]

15.24
[.600]

12

19.81
[.780]

26

8

8-104666-1

21.44
[.844]

13.97
[.550]

11

18.54
[.730]

24

8

8-104666-0

16.36
[.644]

8.89
[.350]

7

13.46
[.530]

16

8

7-104666-9

49.38
[1.944]

46.99
[1.850]

33

46.48
[1.830]

68

8

7-104666-8

44.30
[1.744]

36.83
[1.450]

29

41.40
[1.630]

60

8

7-104666-7

69.70
[2.744]

62.23
[2.450]

49

66.80
[2.630]

100

7-104666-6

57.00
[2.244]

49.53
[1.950]

39

54.10
[2.130]

80

8

7-104666-5

37.95
[1.494]

30.48
[1.200]

24

35.05
[1.380]

50

8

7-104666-4

31.60
[1.244]

24.13
[.950]

19

28.70
[1.130]

40

7-104666-3

25.25
[.994]

17.78
[.700]

14

22.35
[.880]

30

8

7-104666-2

18.90
[.744]

11.43
[.450]

9

16.00
[.630]

20

7-104666-1

7

27.79
[1.094]

20.32
[.800]

15

24.89
[.980]

34

9

6-104666-3

12.55
[.494]

5.08
[.200]

4

9.65
[.380]

10

9

6-104666-2

22.71
[.894]

15.24
[.600]

12

19.81
[.780]

26

9

6-104666-1

21.44
[.844]

13.97
[.550]

11

18.54
[.730]

24

9

6-104666-0

16.36
[.644]

8.89
[.350]

7

13.46
[.530]

16

9

5-104666-9

49.38
[1.944]

46.99
[1.850]

33

46.48
[1.830]

68

9

5-104666-8

44.30
[1.744]

36.83
[1.450]

29

41.40
[1.630]

60

9

5-104666-7

69.70
[2.744]

62.23
[2.450]

49

66.80
[2.630]

100

9

5-104666-6

57.00
[2.244]

49.53
[1.950]

39

54.10
[2.130]

80

9

5-104666-5

37.95
[1.494]

30.48
[1.200]

24

35.05
[1.380]

50

9

5-104666-4

31.60
[1.244]

24.13
[.950]

19

28.70
[1.130]

40

9

5-104666-3

25.25
[.994]

17.78
[.700]

14

22.35
[.880]

30

9

5-104666-2

18.90
[.744]

11.43
[.450]

9

16.00
[.630]

20

9

5-104666-1

FINISH

G

C

B

A

NO OF POSN

PART NUMBER

10

27.79
[1.094]

20.32
[.800]

15

24.89
[.980]

34

8

3-104666-3

12.55
[.494]

5.08
[.200]

4

9.65
[.380]

10

3-104666-2

22.71
[.894]

15.24
[.600]

12

19.81
[.780]

26

8

3-104666-1

21.44
[.844]

13.97
[.550]

11

18.54
[.730]

24

8

3-104666-0

16.36
[.644]

8.89
[.350]

7

13.46
[.530]

16

8

2-104666-9

49.38
[1.944]

46.99
[1.850]

33

46.48
[1.830]

68

8

2-104666-8

44.30
[1.744]

36.83
[1.450]

29

41.40
[1.630]

60

8

2-104666-7

69.70
[2.744]

62.23
[2.450]

49

66.80
[2.630]

100

8

2-104666-6

57.00
[2.244]

49.53
[1.950]

39

54.10
[2.130]

80

8

2-104666-5

37.95
[1.494]

30.48
[1.200]

24

35.05
[1.380]

50

8

2-104666-4

31.60
[1.244]

24.13
[.950]

19

28.70
[1.130]

40

8

2-104666-3

25.25
[.994]

17.78
[.700]

14

22.35
[.880]

30

8

2-104666-2

18.90
[.744]

11.43
[.450]

9

16.00
[.630]

20

8

2-104666-1

1

27.79
[1.094]

20.32
[.800]

15

24.89
[.980]

34

12

1-104666-3

12.55
[.494]

5.08
[.200]

4

9.65
[.380]

10

12

1-104666-2

22.71
[.894]

15.24
[.600]

12

19.81
[.780]

26

1-104666-1

21.44
[.844]

13.97
[.550]

11

18.54
[.730]

24

1-104666-0

16.36
[.644]

8.89
[.350]

7

13.46
[.530]

16

104666-9

49.38
[1.944]

46.99
[1.850]

33

46.48
[1.830]

68

104666-8

44.30
[1.744]

36.83
[1.450]

29

41.40
[1.630]

60

104666-7

69.70
[2.744]

62.23
[2.450]

49

66.80
[2.630]

100

104666-6

57.00
[2.244]

49.53
[1.950]

39

54.10
[2.130]

80

104666-5

37.95
[1.494]

30.48
[1.200]

24

35.05
[1.380]

50

104666-4

31.60
[1.244]

24.13
[.950]

19

28.70
[1.130]

40

104666-3

25.25
[.994]

17.78
[.700]

14

22.35
[.880]

30

104666-2

18.90
[.744]

11.43
[.450]

9

16.00
[.630]

20

104666-1

FINISH

G

C

B

A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN BSV

19AUG04

CHK

—

TE

TE Connectivity

DIMENSIONS: mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13[.005]

3 PLC ± -

4 PLC ± -

ANGLES

MATERIAL

FINISH

SEE TABLE

APVD D L SIMPSON

PRODUCT SPEC

108-1093

APPLICATION SPEC

114-25031

WEIGHT

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A100779

104666

—

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV AB1

4805 (3/11)