




3M™ RIBBON CABLE WIREMOUNT SOCKET ASSEMBLY, 451 SERIES
.050" X .050" (1.27MM X 1.27MM) FOR .025" PITCH CABLE





CENTER POLARIZATION
AND FRICTION LATCH




CENTER POLARIZATION
AND NO FRICTION LATCH





NO CENTER POLARIZATION
AND NO FRICTION LATCH




PRE-POSITIONED COVER



WITH OPTIONAL
STRAIN RELIEF



NO STRAIN RELIEF



TERMINATED
CONNECTOR

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

PERFORMANCE:	
CURRENT RATING:	1.0A, UL 04P-50P, NOT FOR CURRENT INTERRUPTION 1.0A, CUL 04P-30P, NOT FOR CURRENT INTERRUPTION 0.75A, CUL 32P-50P, NOT FOR CURRENT INTERRUPTION 0.75A, ALL LINES ENERGIZED, 30°C TEMP RISE PER EIA 364-70 1.50A, 6 LINES ENERGIZED, 30°C TEMP RISE PER EIA 364-70
UL & CUL VOLTAGE RATING:	125V _{AC}
INSULATION RESISTANCE:	> 1 × 10 ⁹ Ohms AT 500 VDC
WITHSTANDING VOLTAGE:	1250V _{DC} AT SEA LEVEL
OPERATING TEMPERATURE:	-65°C TO +125°C
UL & CUL OPERATING TEMPERATURE:	+130°C

- NOTES
- MATERIAL:
BODY: PBT, UL94V-0
COVER: PBT, UL94V-0
STRAIN RELIEF: STAINLESS STEEL
CONTACTS: BeCu ALLOY.
 - PLATING:
50-150μ" NICKEL UNDERPLATE
30 = 30μ" MIN. GOLD ON WIPING AREA
00 = FLASH GOLD ON WIPING AREA.
 - RIBBON CABLE COMPATIBILITY:
GENERAL:
0.025" PITCH, 30 AWG, SOLID OR STRANDED.
RECOMMENDED CABLE:
SEE TABLE 2 FOR CABLE COMPATIBILITY.
 - MATING COMPATIBILITY:
3M 1.27mm (0.050"), SERIES 452 HEADER WITH LATCH/EJECT OPTION. TECH SHEETS TS-2437 AND TS-2396
 - REGULATORY INFORMATION:
VISIT 3M.com/regs
 - IN THE EVENT OF CONFLICT BETWEEN THIS DATA AND THAT CONTAINED IN THE PRODUCT SPECIFICATION, THE PRODUCT SPECIFICATION TAKES PRECEDENT.
 - REFERENCE RELATED DOCUMENTS:
PRODUCT SPECIFICATION:
3M DOC. ID# 78-5102-0091-4.
 - TOOLING AND INSTALLATION INSTRUCTIONS:
3M DOC. ID# 78-9101-8937-8.
 - OTHER PIN COUNTS AVAILABLE UPON REQUEST. CONTACT 3M.
 - PACKAGING:
SOCKET: TRAY
COVER: BAG

ORDERING INFORMATION
FOR RAPID INSTALLATION ON
RIBBON CABLE APPLICATIONS

451 XX - 0 X 0 0 XX

SERIES

NUMBER OF POSITIONS
SEE TABLE 1

PLATING
00 = AU FLASH
30 = 30μ" GOLD

OPTIONAL FEATURES
0 = NONE SPECIFIED

PACKAGING
0 = STANDARD (TRAYS)

CENTER POLARIZATION / FRICTION LATCH
0 = NO CENTER POLARIZATION (CP) (ALL POS.)
1 = CP NO FRICTION LATCH (08 AND HIGHER POS.)
2 = CP WITH FRICTION LATCH (08 AND HIGHER POS.)


NOTE:
FRICTION LATCH (OPTION 2) IS NOT SUITABLE
FOR HEADER WITH LATCH EJECT OPTION

ACCESSORY: STRAIN RELIEF
3448-451XX

NUMBER OF POSITIONS



APPLICATION TOOLING:
ALUMINUM: 3443-82-XX

NUMBER OF POSITIONS





78-5100-2396-9 78-5100-2437-1		NEXT ASSEMBLY		PRODUCTION RELEASE					
DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
DESIGN CODES		DESIGN CODES		DRFT	ARM	DATE FEB 11, 2011		MFG	DATE
DESIGN CODES		DESIGN CODES		CHKD	ARM	DATE		APPR SAN	DATE FEB 11, 2011
DIVISION		DIVISION CODE EMSD		3M 3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2022 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
DO NOT SCALE DRAWING		SCALE 1 I		TOLERANCES EXCEPT AS NOTED					
		THIRD ANGLE PROJECTION		INCHES .00 ± .01 .00 ± .02 .000 ± .010 .0000 ± .005		TITLE RIBBON CABLE WMT SOCKET, .05 X .05 PITCH, 451 SERIES			
INTERPRET PER ASME Y14.5 - 2018		MILLIMETERS 0 ±		CAGE NUMBER		SIZE		DRAWING NO. 78-5100-2436-3	
MAX SURFACE ROUGHNESS ✓  ALL SURFACES □ MARKED ONLY		ANGLES ±		MODEL 451		DET. LISTS		YES ☒ NO ☐	
								SHT 1 OF 3	

UL FILE NO: E68080

3M™ RIBBON CABLE WIREMOUNT SOCKET ASSEMBLY, 451 SERIES
.050" X .050" (1.27MM X 1.27MM) FOR .025" PITCH CABLE



COVER



ACCESSORY - STRAIN RELIEF
PART NUMBER 3448-451XX

TABLE 1			
No. Positions	Dim "A"	Dim "B"	Dim "C"
4	.050	.210	.270
6	.100	.260	.320
8	.150	.310	.370
10	.200	.360	.420
12	.250	.410	.470
14	.300	.460	.520
16	.350	.510	.570
20	.450	.610	.670
26	.600	.760	.820
30	.700	.860	.920
40	.950	1.110	1.170
50	1.200	1.360	1.420

TABLE 2	
COMPATABLE RIBBON CABLE	
1	3M™ ROUND CONDUCTOR FLAT CABLE, 3754 SERIES: PVC, ROUND STRANDED CONDUCTOR
2	3M™ ROUND CONDUCTOR FLAT CABLE, 3447 SERIES: PVC, ROUND SOLID CONDUCTOR
3	3M™ ROUND CONDUCTOR FLAT CABLE, 3756 SERIES: TPE, ROUND STRANDED CONDUCTOR
4	3M™ ROUND CONDUCTOR FLAT CABLE, 3749 SERIES: TPE, ROUND SOLID CONDUCTOR
5	3M™ ROUND CONDUCTOR FLAT CABLE, 3609 SERIES: FEP, ROUND STRANDED CONDUCTOR
6	3M™ ROUND CONDUCTOR FLAT CABLE, 3604 SERIES: FEP, ROUND SOLID CONDUCTOR
7	3M™ ROUND CONDUCTOR FLAT CABLE, HF447 SERIES: PO, HALOGEN FREE, ROUND SOLID CONDUCTOR
8	3M™ ROUND CONDUCTOR FLAT CONTROLLED IMPEDANCE CABLE, 7700 SERIES: PO, SHIELDED, ROUND SOLID CONDUCTOR

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

K	106347	AUG 19,2022 ADD TABLE 2 FOR CABLE	JNC	SAN
J	105041	MAY 26,2022 REVISE PERFORMANCE SECTION	JNC	SAN
H	100200	OCT 19,2021 ADD POS 26, 40, 50	JNC	SAN
G	92270	AUG 19,2020 ADD NOTES AND VIEWS	JNC	SAN
F	56988	SEP 24,2014 REVISE PERFORMANCE CHART	JNC	SN
E	54514	MAY 07,2014 ADD UL LOGO	SJS	SAN
D	51884	JAN 08,2014 ADD DESIGN REF, UPDATE TITLE, ADD TS	SJS	SAN
C	50290	OCT 08,2013 REVISE NOTES 1, 3, 8 & OPERATING TEMP.	JNC	SN
B	48635	JUL 12,2013 MATCH TEXT FONTS & ADD NOTE 10	JNC	SN
A	46797	MAR 25,2013 PRODUCTION RELEASE	JNC	SAN
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	ARM	DATE FEB 11,2011	MFG	DATE
CHKD	DATE	APPRV SAN	DATE	FEB 11,2011

78-5100-2396-9 78-5100-2437-1		NEXT ASSEMBLY	
DESIGN REFERENCE	DIVISION CODE	EMSD	
DO NOT SCALE DRAWING	SCALE 4/1	TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5 - 2018	INCHES .0 ±.1 .00 ±.02 .000 ±.010 .0000 ±.005	MILLIMETERS 0 ± .0 ± .00 ± .000 ±
MAX SURFACE ROUGHNESS	ALL SURFACES	ANGLES	
MARKED ONLY			

3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2022 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.	
TITLE		RIBBON CABLE WMT SOCKET, .05 X .05 PITCH, 451 SERIES	
CAGE NUMBER	SIZE	DRAWING NO.	REV.
D	78-5100-2436-3	K	
MODEL	451	LISTS	YES NO
SHT 2 OF 3			

3M™ RIBBON CABLE WIREMOUNT SOCKET ASSEMBLY, 451 SERIES

.050" X .050" (1.27MM X 1.27MM) FOR .025" PITCH CABLE

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company
Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

		K	106347	AUG 19,2022 ADD TABLE 2 FOR CABLE		JNC	SN
		J	105041	MAY 26,2022 REVISE PERFORMANCE SECTION		JNC	SN
		H	100200	OCT 19,2021 ADD POS 26 , 40 , 50		JNC	SN
		G	92270	AUG 19,2020 ADD NOTES AND VIEWS		JNC	SN
		F	56988	SEP 24,2014 REVISE PERFORMANCE CHART		JNC	SN
		E	54514	MAY 07,2014 ADD UL LOGO		SJS	SN
		D	51884	JAN 08,2014 ADD DESIGN REF, UPDATE TITLE, ADD TS REF		SJS	SN
		C	50290	OCT 08,2013 REVISE NOTES 1 , 3 , 8 & OPERATING TEMP.		JNC	SN
		B	48635	JUL 12,2013 MATCH TEXT FONTS & ADD NOTE 10		JNC	SN
		A	46797	MAR 25,2013 PRODUCTION RELEASE		JNC	SN
		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
78-5100-2396-9 78-5100-2437-1 DESIGN REFERENCE		NEXT ASSEMBLY		DRFT A10M	DATE FEB 11,2011	MFG SAN	DATE
ADDRESS CODES				CHKD	DATE	APPL SAN	DATE FEB 11,2011
DIVISION		TOLERANCES EMSD		TITLE			
DO NOT SCALE DRAWING		SCALE 4 1		3M 3M Center St. Paul, MN 55144			
THIRD ANGLE PROJECTION		TOLERANCES EXCEPT AS NOTED		© 3M COPYRIGHT 2022 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
INTERPRET PER ASME Y14.5 - 2018		INCHES .0 ± .1 .00 ± .02 .000 ± .010 .0000 ± .005		RIBBON CABLE WMT SOCKET , .05 X .05 PITCH , 451 SERIES			
MAX SURFACE ROUGHNESS		MILLIMETERS 0 ± .0 .00 ± .000 ±		CAGE NUMBER		SIZE DRAWING NO.	
☒ ALL SURFACES ☐ MARKED ONLY		ANGLES ±		D 78-5100-2436-3		REV. K	
		MODEL 451		DET. LISTS ☒ YES ☐ NO		SHT 3 OF 3	