


THIS DRAWING IS A CONTROLLED DOCUMENT  
REV 17579

Restricted to: General Release

USED ON




#### Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: MM

Housing Color: Red

Geom. Spec: 115-1215



VIEW C-C  
NOT TO SCALE

#### Fiber Path

Fiber A - ——— - Fiber B  
Fiber B - ——— - Fiber A

#### Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).

#### Right Side

Connector(s): SC-Duplex

Mode: MM

Housing Color: Beige

Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC  
CE  
DIST  
16

CAC Customer Layout Rev: D

|   |     |             |               |           |    |      |  |
|---|-----|-------------|---------------|-----------|----|------|--|
|   |     |             |               |           |    |      |  |
|   | B   | Rev Per EC# | ECR-06-020123 | 9/21/2006 | -  | MK   |  |
| P | LTR | REVISION    | RECORD        | DATE      | DN | APVD |  |

| DIMENSIONS: |
|-------------|
| meters      |

| TOLERANCES UNLESS OTHERWISE SPECIFIED: |
|----------------------------------------|
| 0 P.L.C. ± .                           |
| 1 P.L.C. ± .                           |
| 2 P.L.C. ± .                           |
| 3 P.L.C. ± .                           |
| 4 P.L.C. ± .                           |



Customer Print

|       |                                                                                         |            |            |
|-------|-----------------------------------------------------------------------------------------|------------|------------|
| DIN   | Cable Assy Configurator                                                                 | MATERIAL   | HEAT TREAT |
| CHK   | Michael Kepko                                                                           |            |            |
| APVD  | Michael Kepko                                                                           |            |            |
| NAME  | FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex |            |            |
| SCALE | SIZE                                                                                    | DRAWING NO | SHEET      |
| NTS   | A2                                                                                      | C- 6754410 | 1 of 3     |
|       |                                                                                         |            | REV B      |

**AMP** Tyco Electronics, Inc.  
Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC  
CE  
DIST  
16

Restricted to: General Release

USED ON

| Part #      | L (meters)      | L (feet)        | MT-RJ SECURE (No Pins), Red |         | SC-Duplex, Beige |         |
|-------------|-----------------|-----------------|-----------------------------|---------|------------------|---------|
|             |                 |                 | IL (dB)                     | RL (dB) | IL (dB)          | RL (dB) |
| 0-6754410-1 | 0.950 - 1.050   | 3.11 - 3.44     | 0.5                         | 20      | 0.5              | -       |
| 0-6754410-2 | 1.950 - 2.050   | 6.39 - 6.72     | 0.5                         | 20      | 0.5              | -       |
| 0-6754410-3 | 2.950 - 3.050   | 9.67 - 10.00    | 0.5                         | 20      | 0.5              | -       |
| 0-6754410-4 | 3.920 - 4.080   | 12.86 - 13.38   | 0.51                        | 20      | 0.51             | -       |
| 0-6754410-5 | 4.920 - 5.080   | 16.14 - 16.66   | 0.51                        | 20      | 0.51             | -       |
| 0-6754410-6 | 5.920 - 6.080   | 19.42 - 19.94   | 0.51                        | 20      | 0.51             | -       |
| 0-6754410-7 | 6.920 - 7.080   | 22.70 - 23.22   | 0.51                        | 20      | 0.51             | -       |
| 0-6754410-8 | 7.920 - 8.080   | 25.98 - 26.50   | 0.51                        | 20      | 0.51             | -       |
| 0-6754410-9 | 8.850 - 9.150   | 29.03 - 30.01   | 0.51                        | 20      | 0.51             | -       |
| 1-6754410-0 | 9.850 - 10.150  | 32.31 - 33.30   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-1 | 10.850 - 11.150 | 35.59 - 36.58   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-2 | 11.850 - 12.150 | 38.87 - 39.86   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-3 | 12.850 - 13.150 | 42.15 - 43.14   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-4 | 13.850 - 14.150 | 45.43 - 46.42   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-5 | 14.850 - 15.150 | 48.72 - 49.70   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-6 | 15.840 - 16.160 | 51.96 - 53.01   | 0.52                        | 20      | 0.52             | -       |
| 1-6754410-7 | 16.830 - 17.170 | 55.21 - 56.33   | 0.53                        | 20      | 0.53             | -       |
| 1-6754410-8 | 17.820 - 18.180 | 58.46 - 59.64   | 0.53                        | 20      | 0.53             | -       |
| 1-6754410-9 | 18.810 - 19.190 | 61.71 - 62.95   | 0.53                        | 20      | 0.53             | -       |
| 2-6754410-0 | 19.800 - 20.200 | 64.96 - 66.27   | 0.53                        | 20      | 0.53             | -       |
| 2-6754410-1 | 20.790 - 21.210 | 68.20 - 69.58   | 0.53                        | 20      | 0.53             | -       |
| 2-6754410-2 | 21.780 - 22.220 | 71.45 - 72.90   | 0.53                        | 20      | 0.53             | -       |
| 2-6754410-3 | 22.770 - 23.230 | 74.70 - 76.21   | 0.53                        | 20      | 0.53             | -       |
| 2-6754410-4 | 23.760 - 24.240 | 77.95 - 79.52   | 0.54                        | 20      | 0.54             | -       |
| 2-6754410-5 | 24.750 - 25.250 | 81.20 - 82.84   | 0.54                        | 20      | 0.54             | -       |
| 2-6754410-6 | 25.740 - 26.260 | 84.44 - 86.15   | 0.54                        | 20      | 0.54             | -       |
| 2-6754410-7 | 26.730 - 27.270 | 87.69 - 89.46   | 0.54                        | 20      | 0.54             | -       |
| 2-6754410-8 | 27.720 - 28.280 | 90.94 - 92.78   | 0.54                        | 20      | 0.54             | -       |
| 2-6754410-9 | 28.710 - 29.290 | 94.19 - 96.09   | 0.54                        | 20      | 0.54             | -       |
| 3-6754410-0 | 29.700 - 30.300 | 97.44 - 99.40   | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-1 | 30.690 - 31.310 | 100.68 - 102.72 | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-2 | 31.680 - 32.320 | 103.93 - 106.03 | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-3 | 32.670 - 33.330 | 107.18 - 109.35 | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-4 | 33.660 - 34.340 | 110.43 - 112.66 | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-5 | 34.650 - 35.350 | 113.68 - 115.97 | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-6 | 35.640 - 36.360 | 116.92 - 119.29 | 0.55                        | 20      | 0.55             | -       |
| 3-6754410-7 | 36.630 - 37.370 | 120.17 - 122.60 | 0.56                        | 20      | 0.56             | -       |
| 3-6754410-8 | 37.620 - 38.380 | 123.42 - 125.91 | 0.56                        | 20      | 0.56             | -       |
| 3-6754410-9 | 38.610 - 39.390 | 126.67 - 129.23 | 0.56                        | 20      | 0.56             | -       |
| 4-6754410-0 | 39.600 - 40.400 | 129.92 - 132.54 | 0.56                        | 20      | 0.56             | -       |
| 5-6754410-0 | 49.500 - 50.500 | 162.40 - 165.68 | 0.58                        | 20      | 0.58             | -       |

| Qty | U of M | Description                                            | Item No. |
|-----|--------|--------------------------------------------------------|----------|
| 1   | piece  | DUST COVER, MT-RJ                                      | 1        |
| 1   | piece  | SPRING, MT-RJ, 3.8 DESIGN                              | 2        |
| 1   | piece  | PIN KEEPER, 3.8MM                                      | 3        |
| 1   | piece  | MT-RJ, SPRING PUSH, UNIVERSAL                          | 4        |
| 1   | piece  | CRIMP EYELET, MT-RJ                                    | 5        |
| 1   | piece  | MT-RJ Keyed Connector Housing - Red                    | 6        |
| 2   | piece  | LC, SC, FC Straight Boot, Beige                        | 7        |
| 1   | piece  | MT-RJ FERRULE, THERMOPLAST,MM                          | 8        |
| 2   | piece  | SC Simplex Housing, Beige                              | 9        |
| 2   | piece  | 2.5mm ferrule cover                                    | 10       |
| AR  | meter  | 2 fiber, XG-50/125, 1.8mm, Twinzip, Aqua, OFNR (Riser) | 11       |
| 1   | piece  | MT-RJ TwinZip Bend Limiting Boot, Beige                | 12       |
| 2   | piece  | SC Duplex Clip                                         | 13       |
| 2   | piece  | Eyelet/Shrink tube assembly - White                    | 14       |
| 2   | piece  | CONN SUBASSY, MM, SC 1.6MM                             | 15       |
| 2   | piece  | Trace Label                                            | 16       |

|   |     |                 |               |           |      |
|---|-----|-----------------|---------------|-----------|------|
|   |     |                 |               |           |      |
|   | B   | Rev Per EC#     | ECR-06-020123 | 8/21/2006 | - MK |
| P | LTR | REVISION RECORD | DATE          | DIN       | APVD |

DIMENSIONS:  
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ±  
1 P.L.C. ±  
2 P.L.C. ±  
3 P.L.C. ±  
4 P.L.C. ±

Customer Print

|       |                                                                                         |            |                                                     |            |  |
|-------|-----------------------------------------------------------------------------------------|------------|-----------------------------------------------------|------------|--|
| DIN   | Cable Assy Configurator                                                                 |            | MATERIAL                                            | HEAT TREAT |  |
| CHK   | Michael Kepko                                                                           |            | Tyco Electronics, Inc.<br>Harrisburg, PA 17105-3608 |            |  |
| APVD  | Michael Kepko                                                                           |            |                                                     |            |  |
| NAME  | FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex |            |                                                     |            |  |
| SCALE | SIZE                                                                                    | DRAWING NO | SHEET                                               | REV        |  |
| NTS   | A2                                                                                      | C- 6754410 | 2 of 3                                              | B          |  |

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

1