

SC-RJ female insert - VS-SCRJ-GOF-BU/BU - 1652978

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



SC-RJ socket insert, duplex, for VS-A-F-IP67 panel mounting frame, can be used for fiberglass (multi-mode and single mode), PCF, and polymer fibers

Your advantages

- ✓ suitable for fiber types:
 - POF (980/1000 µm)
 - PCF (200/230 µm)
 - GOF MM (50/125 µm and 62.5/125 µm)
 - GOF SM (9/125 µm)



Ethernet

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 969943
GTIN	4017918969943

Technical data

Mechanical characteristics

Number of positions	2
Number of slots	2
Connection profile	SC-RJ, according to DIN EN 50377-6-1
Fiber type	GOF, PCF, POF
Ferrule diameter	2.50 mm
Number of fibers	2
Insertion/withdrawal cycles	≥ 500
Connection method	Coupling
Color	black
Degree of protection	IP20

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
---------------------------------	------------------

SC-RJ female insert - VS-SCRJ-GOF-BU/BU - 1652978

Technical data

Ambient conditions

Degree of protection	IP20
----------------------	------

Material data

Flammability rating according to UL 94	V0
Housing material	PBT
Ferrule material	Zirconia ceramics
Ferrule holder color	white

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>