




PRODUCT N°: SEE SHEET 213-2 OF 2




R TO FULL RADIUS ALLOWED TYP

("K")



NOTES:

1. MATERIAL HOUSING: THERMOPLASTIC POLYESTER, 30% GLASFILLED, COLOUR BLUE, FLAME RETARDANT PER UL 94-V0.
2. MATERIAL BOX: BRASS ASTM B36 C26000-H02
3. MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194 C17200-TF 00
4. PLATING: SEE SHEET 213-2 OF 2



CUSTOMER COPY FOR REFERENCE ONLY			
BERG ELECTRONICS DIVISION DUPONT DE NEMOURS NEDERLAND BV			
SEE NOTES	SEE NOTE 4	B ECP BEU 5095	76 325
PART NO	MATERIAL	A ECP BEU 4659	H B
PLATING	RELEASED 0670	RELEASED 0670	SHEET 213 - 1 OF 2
VERTICAL CARD CONNECTOR			
5:1 double row 100x100			

76 325
SHEET 213 - 1 OF 2

PRODUCT	NO	NO OF POS	DIM. ('J')	DIM. ('K')
76325	- X02	2 x 02	2.54 100	5.08 200
	- X03	2 x 03	5.08 200	7.62 300
	- X04	2 x 04	7.62 300	10.16 400
	- X05	2 x 05	10.16 400	12.70 500
	- X06	2 x 06	12.70 500	15.24 600
	- X07	2 x 07	15.24 600	17.78 700
	- X08	2 x 08	17.78 700	20.32 800
	- X09	2 x 09	20.32 800	22.86 900
76325	- X10	2 x 10	22.86 900	25.40 1,000
	- X11	2 x 11	25.40 1,000	27.94 1,100
	- X12	2 x 12	27.94 1,100	30.48 1,200
	- X13	2 x 13	30.48 1,200	33.02 1,300
	- X14	2 x 14	33.02 1,300	35.56 1,400
	- X15	2 x 15	35.56 1,400	38.10 1,500
	- X16	2 x 16	38.10 1,500	40.64 1,600
	- X17	2 x 17	40.64 1,600	43.18 1,700
	- X18	2 x 18	43.18 1,700	45.72 1,800
	- X19	2 x 19	45.72 1,800	48.26 1,900
76325	- X20	2 x 20	48.26 1,900	50.80 2,000
	- X21	2 x 21	50.80 2,000	53.34 2,100
	- X22	2 x 22	53.34 2,100	55.88 2,200
	- X23	2 x 23	55.88 2,200	58.42 2,300
	- X24	2 x 24	58.42 2,300	60.96 2,400
	- X25	2 x 25	60.96 2,400	63.50 2,500
	- X26	2 x 26	63.50 2,500	66.04 2,600
	- X27	2 x 27	66.04 2,600	68.58 2,700
	- X28	2 x 28	68.58 2,700	71.12 2,800
	- X29	2 x 29	71.12 2,800	73.66 2,900
76325	- X30	2 x 30	73.66 2,900	76.20 3,000

PRODUCT NO	NO OF POS	DM. ('J')	DM. ('K')
76325 - X31	2 x 31	78.28 3.000	78.75 3.104
- X32	2 x 32	78.75 3.100	81.28 3.200
- X33	2 x 33	81.29 3.200	83.82 3.300
- X34	2 x 34	83.82 3.300	86.34 3.400
- X35	2 x 35	86.34 3.400	88.90 3.500
- X36	2 x 36	88.90 3.500	91.44 3.600
- X37	2 x 37	91.44 3.600	93.98 3.700
- X38	2 x 38	93.98 3.700	96.52 3.800
- X39	2 x 39	96.52 3.800	99.06 3.900
76325 - X40	2 x 40	99.06 3.900	101.60 4.000
- X41	2 x 41	101.60 4.000	104.14 4.100
- X42	2 x 42	104.14 4.100	106.68 4.200
- X43	2 x 43	106.68 4.200	109.22 4.300
- X44	2 x 44	109.22 4.300	111.76 4.400
- X45	2 x 45	111.76 4.400	114.30 4.500
- X46	2 x 46	114.30 4.500	116.84 4.600
- X47	2 x 47	116.84 4.600	119.38 4.700
- X48	2 x 48	119.38 4.700	121.92 4.800
- X49	2 x 49	121.92 4.800	124.46 4.900
76325 X50	2 x 50	124.46 4.900	127.00 5.000

4	$\frac{1.9}{75} \frac{\mu\text{m}}{\mu\text{inch}}$ Au	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Ni MINIMUM	
3	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Au	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Ni MINIMUM	
2	$\frac{1.0}{40} \frac{\mu\text{m}}{\mu\text{inch}}$ Au	$\frac{1.3}{50} \frac{\mu\text{m}}{\mu\text{inch}}$ Ni MINIMUM	
X	PLATING THICKNESS	THICKNESS	

CUSTOMER COPY FOR REFERENCE ONLY			
NO POSTAGE NECESSARY IF MAILED IN THE UNITED STATES			
MATERIAL SEE TABLE MEAT TREAT	DR AOSTERVELD 830303 CNR M. LARSEN	DATE DATE REL. 83	APP. <i>[Signature]</i> <i>W. H. Hansen</i>
PINN SEE TABLE LAYOUT	NEW BORG ELECTRONICS DIVISION HERIOTHOESBOSCH HOLLAND		
POSTAL	SITE	DWG NO 76325	
C	SERIAL 213-2 of 2		

PDMD Rev: B STATUS: Released Print Date: Sep 2003 2005

76325

5

4

3




2

1

PRODUCT N° 76325-XXX

THIRD ANGLE
PROJECTION

DU PONT

This print is the property of and embodies proprietary designs of the BERG ELECTRONICS DIVISION of
DU PONT DE NEMOURS (NEDERLAND) B.V. No part of the design shown on this print may be used in
any way without the written consent of BERG ELECTRONICS DIVISION, s-Hertogenbosch, Holland.DIMENSIONS $\frac{\text{mm}}{\text{INCHES}}$
DO NOT SCALERECOMMENDED
PIN PATTERNRECOMMENDED
HOLE PATTERN

NOTES :

1. THICKNESS P.C. BOARD INCLUDING METAL FOIL 1.60 ± 0.20 ($.063 \pm .008$)
2. TERMINALS CAN ONLY BE USED FOR P.C. BOARD APPLICATION WITH NON-PLATED THROUGH HOLES.
3. PRODUCT TO MATE WITH 0.635 ± 0.025 ($.025 \pm .001$) SQUARE PIN OR ROUND PIN.

CUSTOMER COPY FOR REFERENCE ONLY

BERG ELECTRONICS DIVISION
DU PONT DE NEMOURS (NEDERLAND) B.V.
s-hertogenbosch holland

PART NO. MATERIAL PLATING

DR R. SCHELLEKENS DATE OCT 30 APP 21 NOV 30

CHK M. 40 DATE NOV 80 REL DATE

RELEASED 0670

SCALE 10:1

TITLE

LOC SIZE NO 76325 REV

H B SHEET 215 1 OF 1

VERTICAL CARD CONNECTOR

double row.100x.100