


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- . - .
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		N	REVISED PER ECO-11-008643	26APR11	RC	CW
			P	ECO-11-024491	13DEC11	SY	MQW
			R	ECR-12-009867	25NOV12	SY	AC

D




C

B




NOTES:

- 1 MATERIAL CONTACT: PHOSPHORBRONZE
MATERIAL HOUSING: GLASSFILLED POLYESTER
UL-RATING 94VO (GRAY).
- 2 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm
NICKEL MIN. AND ACTION PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE
FOR EACH DASH NUMBER.
- 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE
LEVEL 2.
- 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE
LEVEL 1.
- 5 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- 6 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
- 7 CONNECTOR LUBRICATED WITH TELCORDIA APPROVED LUBRICANT.
- 8 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
- 9 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (125 HOLES).
- 10 HOLES IN ROW f AND z FOR POSSIBLE FUTURE USE OF
GROUND RETURN SHIELD. (SHIELDS NOT YET TOOLED)
- 11 0.76µm MIN GOLD PLATING AT MATING SURFACES.




COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT

P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION



SECTION A-A



OBSOLETE			3-106774-0
			1-106774-9
			106774-9
			106774-4
			106774-1
	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	—	TE Connectivity									
		CHK —	—										
		APVD —	—	NAME									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		Z-PACK 2MM HM TYPE B 125 POS. VERTICAL FEMALE CONNECTOR ASSEMBLY									
		0-PLC ± —		PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
		1-PLC ± — ±0.2											
		2-PLC ± —											
		3-PLC ± —											
		4-PLC ± —											
ANGLES — ± —		FINISH —		WEIGHT —			A2	00779	C=106774	—			
MATERIAL —		CUSTOMER DRAWING		SCALE		SHEET					REV		
				NTS		1 of 1					R		