








PCB CONFIGURATION




VIEW A



RECOMMENDED PANEL CUTOUT

- ① POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:WHITE
- ② POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:BLACK
- ③ POLYESTER PCT GENERAL PURPOSE, 30% GLASS FILLED, UL94V-O RATED, COLOR:GRAY
- ④ POLYMETHYLPENTENE, GENERAL PURPOSE.
- ⑤ ZINC PER QQ-Z-363.
- ⑥ PHOSPHOR BRONZE PER QQ-B-750.
- ⑦ BRASS PER ASTM-B-453.
- ⑧ BRASS PER ASTM-B-16.
- ⑨ NICKEL PLATE PER QQ-N-290,
3.81 μm [.000150] MINIMUM THICK.
- ⑩ TIN PLATE PER ASTM-B-545.
3.81 μm [.000150] MINIMUM THICK.
- ⑪ GOLD PLATE PER MIL-G-45204,
0.76 μm [.000030] MINIMUM THICK.
- ⑫ GOLD PLATE PER MIL-G-45204,
1.27 μm [.000050] MINIMUM THICK.
- ⑬ SILVER PLATE PER QQ-S-365,
2.54 μm [.000100] MINIMUM THICK.
- ⑭ TIN PLATE PER ASTM-B-545,
3.81 μm [.000150] MINIMUM THICK.
15. SEE INSTRUCTION SHEET 2769.
- ⑮ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



VIEW B

16 16	SUPERSEDED BY 5227161-2	14	14	14	14	2	A	—	—	—	9-227161-1
	SUPERSEDED BY 5227161-1	14	14	14	14	1	A	—	—	—	9-227161-0
	SUPERSEDED BY 1-5227161-7	10	10	10	—	—	B	1-329632-2	1-329631-2	227161-9	1-227161-7
	SUPERSEDED BY 1-5227161-6	10	10	10	—	—	B	1-329632-2	1-329631-2	227161-6	1-227161-6
	OBSOLETE	10	10	10	12	1	A	—	—	—	1-227161-4
	SUPSD BY 415218-5 OR 415218-6	10	10	10	11	3	C	—	—	—	1-227161-3
	SUPERSEDED BY 227161-7	10	10	10	—	—	B	1-329632-2	1-329631-2	1-227161-1	1-227161-2
	SUPERSEDED BY 227161-7	10	10	10	11	1	C	—	—	—	1-227161-1
	OBSOLETE	10	10	10	—	—	B	1-329632-2	1-329631-2	227161-3	1-227161-0
		10	10	10	11	2	C	—	—	—	227161-9
	SUPERSEDED BY 227161-7	10	10	10	—	—	B	1-329632-2	1-329631-2	227161-7	227161-8
		10	10	10	11	1	C	—	—	—	227161-7
		10	10	10	11	2	A	—	—	—	227161-6
	SUPERSEDED BY 227161-3	10	10	10	13	1	A	—	—	—	227161-5
	SUPERSEDED BY 227161-6	10	10	10	13	2	A	—	—	—	227161-4
		10	10	10	11	1	A	—	—	—	227161-3
	10	10	10	10	2	A	—	—	—	227161-2	
	10	10	10	10	1	A	—	—	—	227161-1	
	MOUNTING PIN PLATING	GROUND POST PLATING	CONTACT POST PLATING	CONTACT FINISH	HOUSING MATERIAL	VIEW	3 LOCKWASHER	2 JAM NUT QTY=1	1 ASSEMBLY QTY=1	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. LIPPERT	5-2-91	 TE Connectivity
		CHK M. E. COWHER	5-6-91	
		APVD J. LIPPERT	05-09-91	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 2 PLC ± - 3 PLC ± 0.05 [0.002] 4 PLC ± - 5 PLC ± - 6 ANGLES ± ± - FINISH		NAME
		PRODUCT SPEC 108-12078 APPLICATION SPEC		JACK, RIGHT ANGLE, 50 OHM, PCB, BNC
MATERIAL 		WEIGHT -		SIZE CAGE CODE DRAWING NO A1 00779 C-227161
		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE 4:1 SHEET 1 of 1 REV. AF		