



Micro Commercial Corp.  
 21201 Itasca St.  
 Chatsworth, CA 91311  
 Phone: (818) 701-4933  
 Fax: (818) 701-4939

# RL201GP THRU RL207GP

## Features

- Low Cost
- Low Leakage
- Low Forward Voltage Drop
- High Current Capability
- Glass Passivated Junction


## 2 Amp Glass Passivated Rectifier 50 to 1000 Volts

## Maximum Ratings

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Typical Thermal Resistance ( $R_{\theta JA}$ ) 18°C/W

| Microsemi Catalog Number | Device Marking | Maximum Recurrent Peak Reverse Voltage | Maximum RMS Voltage | Maximum DC Blocking Voltage |
|--------------------------|----------------|--|---------------------|-----------------------------|
| RL201GP                  | ---            | 50V                                    | 35V                 | 50V                         |
| RL202GP                  | ---            | 100V                                   | 70V                 | 100V                        |
| RL203GP                  | ---            | 200V                                   | 140V                | 200V                        |
| RL204GP                  | ---            | 400V                                   | 280V                | 400V                        |
| RL205GP                  | ---            | 600V                                   | 420V                | 600V                        |
| RL206GP                  | ---            | 800V                                   | 560V                | 800V                        |
| RL207GP                  | ---            | 1000V                                  | 700V                | 1000V                       |

## DO-15




## Electrical Characteristics @ 25°C Unless Otherwise Specified

|   |             |                                       |   |
|---|-------------|---------------------------------------|---|
| Average Forward Current                                 | $I_{F(AV)}$ | 2 A                                   | $T_A = 75^\circ\text{C}$                              |
| Peak Forward Surge Current                              | $I_{FSM}$   | 60A                                   | 8.3ms, half sine                                      |
| Maximum Instantaneous Forward Voltage                   | $V_F$       | 1.0V                                  | $I_{FM} = 2.0\text{A};$<br>$T_A = 25^\circ\text{C}$   |
| Maximum DC Reverse Current At Rated DC Blocking Voltage | $I_R$       | 5.0 $\mu\text{A}$<br>50 $\mu\text{A}$ | $T_A = 25^\circ\text{C}$<br>$T_A = 100^\circ\text{C}$ |
| Typical Junction Capacitance                            | $C_J$       | 20pF                                  | Measured at<br>1.0MHz, $V_R=4.0\text{V}$              |

\*Pulse Test: Pulse Width 300 $\mu\text{sec}$ , Duty Cycle 1%


| DIM | DIMENSIONS |      |       |      | NOTE |
|-----|------------|------|-------|------|------|
|     | INCHES     |      | MM    |      |      |
| A   | .230       | .300 | 5.80  | 7.60 |      |
| B   | .104       | .140 | 2.60  | 3.60 |      |
| C   | .026       | .034 | .70   | .90  |      |
| D   | 1.000      | ---  | 25.40 | ---  |      |

Figure 1  
Typical Forward Characteristics




Instantaneous Forward Current - MicroAmperes *versus*  
Instantaneous Forward Voltage - Volts

Figure 2  
Forward Derating Curve



Average Forward Rectified Current - Amperes *versus*  
Ambient Temperature - °C


Figure 3  
Junction Capacitance



Junction Capacitance - pF *versus*  
Reverse Voltage - Volts


RL201GP thru RL207GP

Figure 4  
Typical Reverse Characteristics



Instantaneous Reverse Current - Amperes versus  
Percent Of Rated Peak Reverse Voltage - Volts

Figure 5  
Peak Forward Surge Current



Peak Forward Surge Current - Amperes versus  
Number Of Cycles At 60Hz - Cycles