

# PRODUCT NUMBER

98464-X61-XX-XXXLF

PLATING  
S = 0.38µm GOLD/GXT  
ON CONTACT AREA  
2µm MIN MATTE  
TIN ON TAIL

G = 0.76µm GOLD/GXT  
ON CONTACT AREA  
2µm MIN MATTE  
TIN ON TAIL

F = GOLD FLASH ON CONTACT AREA  
2µm MIN MATTE TIN ON TAIL

T = 2.0-5.0µm TIN FULL PLATED  
1.27µm Ni MIN UNDERPLATING

RoHS COMPATIBLE, SEE NOTE 8

POLARIZATION (SEE NOTE 7)

PACKAGING OPTIONAL LETTER (SEE NOTE 5)

TOTAL NB OF POSITIONS, 04 TO 50

COLOR OPTION, NOTE 1

## NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC UL 94V-0

- = STANDARD COLOR CREAM

B = OPTIONAL COLOR BLACK

2. MATERIAL TERMINAL: COPPER ALLOY

3. TO DETERMINE DIMENSIONS:

N = NUMBER OF POSITIONS PER ROW

4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.

5. PACKAGING:

= STANDARD PACKAGING IN POLYBAGS

- = POLYBAGS WHEN POLARISATION FEATURE APPLICABLE

U = TUBE AVAILABLE FROM 06 TO 50 POS

6. DIM "C" = (N x 2.00) + 1.4

EXAMPLE : N = 7

DIM "C" = (7 x 2.00) + 1.4 = 15.4mm

7. FOR POLARIZATION, SPECIFIED PIN

EXAMPLE: A03= ROW A, POSITION 03 TO OMIT PIN

OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE

8. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,

2µm MINIMUM MATTE TIN OVER 1.27µm

MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO

260°C ±5°C SOLDER BATH TEMPERATURE FOR

5 SECONDS IN A WAVE SOLDER APPLICATION

WITH A 1.6mm MIN THICK CIRCUIT BOARD.

- ALSO COMPATIBLE WITH REFLOW PROCESS

260°C PEAK TEMPERATURE FOR 30 SECONDES





MAX IN A CONVECTION, INFRA-RED OR VAPOR

PHASE OR REFLOW OVEN.

c - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - THIS PRODUCT MEETS EUROPEAN DIRECTIVES  
AND OTHER COUNTRY REGULATIONS AS DISCRIBED  
IN GS-47-0004



| mat'l. code |          |       |          | surface                               | tolerance            | projection | product family        |
|-------------|----------|-------|----------|---------------------------------------|----------------------|------------|-----------------------|
| SEE NOTES   |          |       |          | ISO 1302                              | ISO 406              | ISO 1101   | MINITEK               |
| ltr         | ecn no   | dr    | date     | tolerances unless otherwise specified |                      | mm         | title                 |
| L           | B-15815  | JCO   | 13.09.11 | angles                                | X.X ±0.3             |            | SHR HEADER            |
| M           | B-19190  | LMU   | 14.10.24 | linear                                | X.XX ±0.13           |            | 2.00 RIGHT ANGLE TMT  |
| N           | B-19797  | AMA   | 14.12.16 |                                       | X.XXX ±0.05          | scale 1:1  |                       |
| P           | B-19988  | LMU   | 15.01.13 | dr                                    | L.MULIN 04.09.27     |            | dwg no                |
| R           | B-20254  | LMU   | 15.02.16 | engr                                  | J.COMPAGNON 04.09.27 |            | sheet 1 of 1 size     |
| S           | F-32710  | LMU   | 19.02.18 | chr                                   |                      |            | 98464 A3              |
| T           | F-34292  | LMU   | 22.07.19 | appd                                  | JM.C 04.09.27        |            | type CUSTOMER Drawing |
| sheet index | revision | sheet |          |                                       |                      |            |                       |